

Certificate of Suitability

Global-Mark Pty. Ltd., certify the electrical equipment described hereunder complies with standards listed herein and notifies the certificate holder to affix the Regulatory Compliance Mark (RCM) mark on the product of the same type provided that the requirements of all relevant parts of AS/NZS 4417 applicable to the article are fulfilled. In placing the RCM mark on the product, the Responsible Supplier makes a declaration of compliance with the certification standard(s) and confirms that the product is identical to the product certified herein. This Certificate meets the requirements of a Recognised External Certification Scheme (RECS).

CERTIFICATION AND CERTIFICATE HOLDER DETAILS

Company Name	Signify Netherlands B.V	Global-Mark File Number:	105985-046	System 1 Approval
Address	High Tech Campus 48 Eindhoven - 5656 AE Netherlands	Revision Number	00	
Client ID	105985			
Certification Number	GMA-509048			
Certificate Standard(s)	AS 61347.2.13:2018 & AS/NZS 61347.1:2016 + A1 Lamp Control Gear - Part 2-13: Particular Requirements For D.C Or A.C Supplied Electronic Control Gear For Led Modules.			
Type of Certification	Electrical Safety Product Scheme Global-Mark Electrical Product Safety Certification Scheme			

CERTIFICATE DATES

Certificate Issue Date	5/01/2021
Certificate Last Update Date	
Certification Expiry Date	5/01/2026

This certification remains valid until the above mentioned expiry date and subject to the organisation's continued compliance with the certification standard, and Global-Mark's Terms and Conditions. This Certificate remains the property of Global-Mark Pty Ltd, Company Number: ACN.108-087-654. The use of the Accreditation Mark indicates accreditation by the Joint Accreditation System of Australia and New Zealand in respect to those activities covered by JAS-ANZ accreditation. Refer to www.jas-anz.org/register for verification.



Certification Manager



Global-Mark Pty Ltd, Copyright 2012 - 407, 32 Delhi Road, North Ryde NSW 2113, Australia



Certificate of Suitability

CERTIFIED ELECTRICAL EQUIPMENT				
Declared Article	Product Description	Trade Name	Model Number	Rating
Non declared	LED driver - Built in	PHILIPS	Xi 14W/a 0.2-0.35A 40V DS 3CW 230V	Un: 220-240 V; fn: 50/60 Hz; PF: 0,9C; ta: -20...+35 °C; tc: 85 °C; Built-in; 14W,40V
Non declared	LED driver - Built in	PHILIPS	Xi 14W/a 0.2-0.35A 40V DS 3CB 230V	Un: 220-240 V; fn: 50/60 Hz; PF: 0,9C; ta: -20...+35 °C; tc: 85 °C; Built-in; 14W,40V
Non declared	LED driver - Built in	PHILIPS	Xi 14W/a 0.2-0.35A 40V DS 3CG 230V	Un: 220-240 V; fn: 50/60 Hz; PF: 0,9C; ta: -20...+35 °C; tc: 85 °C; Built-in; 14W,40V
Non declared	LED driver - Built in	PHILIPS	Xi 26W/a 0.5-0.65A 40V DS 3CW 230V	Un: 220-240 V; fn: 50/60 Hz; PF: 0,9C; ta: -20...+35 °C; tc: 85 °C; Built-in; 26W,40V
Non declared	LED driver - Built in	PHILIPS	Xi 26W/a 0.5-0.65A 40V DS 3CB 230V	Un: 220-240 V; fn: 50/60 Hz; PF: 0,9C; ta: -20...+35 °C; tc: 85 °C; Built-in; 26W,40V
Non declared	LED driver - Built in	PHILIPS	Xi 26W/a 0.5-0.65A 40V DS 3CG 230V	Un: 220-240 V; fn: 50/60 Hz; PF: 0,9C; ta: -20...+35 °C; tc: 85 °C; Built-in; 26W,40V
Non declared	LED driver - Built in	PHILIPS	Xi 34W/a 0.7-0.85A 40V DS 3CW 230V	Un: 220-240 V; fn: 50/60 Hz; PF: 0,9C; ta: -20...+35 °C; tc: 85 °C; Built-in; 34W,40V
Non declared	LED driver - Built in	PHILIPS	Xi 34W/a 0.7-0.85A 40V DS 3CB 230V	Un: 220-240 V; fn: 50/60 Hz; PF: 0,9C; ta: -20...+35 °C; tc: 85 °C; Built-in; 34W,40V
Non declared	LED driver - Built in	PHILIPS	Xi 34W/a 0.7-0.85A 40V DS 3CG 230V	Un: 220-240 V; fn: 50/60 Hz; PF: 0,9C; ta: -20...+35 °C; tc: 85 °C; Built-in; 34W,40V
Non declared	LED driver - Built in	PHILIPS	Xi 42W/a 0.9-1.05A 40V DS 3CW 230V	Un: 220-240 V; fn: 50/60 Hz; PF: 0,9C; ta: -20...+35 °C; tc: 85 °C; Built-in; 42W,40V
Non declared	LED driver - Built in	PHILIPS	Xi 42W/a 0.9-1.05A 40V DS 3CB 230V	Un: 220-240 V; fn: 50/60 Hz; PF: 0,9C; ta: -20...+35 °C; tc: 85 °C; Built-in; 42W,40V
Non declared	LED driver - Built in	PHILIPS	Xi 42W/a 0.9-1.05A 40V DS 3CG 230V	Un: 220-240 V; fn: 50/60 Hz; PF: 0,9C; ta: -20...+35 °C; tc: 85 °C; Built-in; 42W,40V

This certification remains valid until the above mentioned expiry date and subject to the organisation's continued compliance with the certification standard, and Global-Mark's Terms and Conditions. This Certificate remains the property of Global-Mark Pty Ltd, Company Number: ACN.108-087-654. The use of the Accreditation Mark indicates accreditation by the Joint Accreditation System of Australia and New Zealand in respect to those activities covered by JAS-ANZ accreditation. Refer to www.jas-anz.org/register for verification.



Certification Manager

Global-Mark Pty Ltd, Copyright 2012 - 407, 32 Delhi Road, North Ryde NSW 2113, Australia



Certificate of Suitability

RELEVANT TRADEMARK (S)

COMMENTS OR CONDITIONS ON THE CERTIFICATION
Nil

End of document

This certification remains valid until the above mentioned expiry date and subject to the organisation's continued compliance with the certification standard, and Global-Mark's Terms and Conditions. This Certificate remains the property of Global-Mark Pty Ltd, Company Number: ACN.108-087-654. The use of the Accreditation Mark indicates accreditation by the Joint Accreditation System of Australia and New Zealand in respect to those activities covered by JAS-ANZ accreditation. Refer to www.jas-anz.org/register for verification.



Certification Manager

Global-Mark Pty Ltd, Copyright 2012 - 407, 32 Delhi Road, North Ryde NSW 2113, Australia

