



产品认证证书

证书编号: CQC21010288439

发证日期: 2022 年 09 月 13 日

有效期至: 2032 年 08 月 25 日

委托人名称 昕诺飞(中国)投资有限公司
及注册地址 上海市闵行区田林路 888 弄 9 号楼

制造商名称 昕诺飞(中国)投资有限公司
及注册地址 上海市闵行区田林路 888 弄 9 号楼

生产企业名称
及生产地址

产品名称和系列、规格、型号 灯具用电源导轨系统(导轨接合器(Ⅱ类),集成 LED 模块用交流电子控制装置, ta: 35℃, tc: 80℃, SELV, 适宜直接安装在普通可燃材料表面)
见附件。220-240V ~ 50/60Hz

产品标准和技术要求 IEC 60570: 2019; IEC 60598-1: 2017; GB 7000.1-2015

认证模式 产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC12-465431-2018 认证规则的要求, 特发此证。

本证书为变更证书, 证书首次颁发日期: 2021 年 03 月 08 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站(www.cnca.gov.cn)查验证书信息



签发:

谢肇煦



中国质量认证中心



<http://www.cqc.com.cn>

中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666

C 0533018



CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO.: CQC21010288439

Valid from: Sep.13,2022

Valid until: Aug.25,2032

**NAME AND REGISTERED
ADDRESS OF THE APPLICANT**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND REGISTERED
ADDRESS OF THE
MANUFACTURER**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND LOCATION
OF THE FACTORY**

**PRODUCT NAME, MODEL
AND SPECIFICATION**

Electrical Supply Track System For Luminaires (Track Coupler (ClassII) , Integrated With A.C.
Supplied Electronic Controlgear For LED Modules, ta : 35°C , tc : 80°C , SELV , Suitable For Direct
Mounting On Normally Flammable Material)
See Appendix. 220-240V ~ 50/60Hz

**THE STANDARDS AND
TECHNICAL REQUIREMENTS
FOR THE PRODUCTS**

IEC 60570 : 2019; IEC 60598-1 : 2017; GB 7000.1-2015

**TYPE OF CERTIFICATION
SCHEMES**

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-465431-2018.

Date of original issued: Mar.08,2021

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE



<http://www.cqc.com.cn>

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

Tel: +86 10 83886666

C 0533018



产品认证证书

证书编号 CQC21010288439

第 1 页 共 1 页

本证书及附件应同时使用，信息查验说明见证书页

纸号：533018

序号	产品名称	型号	技术参数
1.	导轨接合器	Xitanium 42W/a 0.15-1.05A 42V MC 3CG	Fmax.50N,Uout:60VdcMax
2.	导轨接合器	Xitanium 42W/a 0.15-1.05A 42V MC 3CW	Fmax.50N,Uout:60VdcMax
3.	导轨接合器	Xitanium 42W/a 0.15-1.05A 42V MC 3CB	Fmax.50N,Uout:60VdcMax
4.	导轨接合器	Xitanium 42W/a 0.15-1.05A 42V 3CG IA	Fmax.50N,Uout:60VdcMax
5.	导轨接合器	Xitanium 42W/a 0.15-1.05A 42V 3CW IA	Fmax.50N,Uout:60VdcMax
6.	导轨接合器	Xitanium 42W/a 0.15-1.05A 42V 3CB IA	Fmax.50N,Uout:60VdcMax

220-240V~,50/60Hz, 导轨接合器(Ⅱ类),集成 LED 模块用交流电子控制装置,ta:35℃,tc:80℃,SELV,适宜直接安装在普通可燃材料表面



中国质量认证中心

