

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT  
(IECEE) CB SCHEME

## CB TEST CERTIFICATE

Product

Electronic controlgear for LED modules

Name and address of the applicant

Signify Netherlands B.V.  
High Tech Campus 48  
5656 AE Eindhoven  
The Netherlands

Name and address of the manufacturer

Signify Netherlands B.V.  
High Tech Campus 48  
5656 AE Eindhoven  
The Netherlands

Name and address of the factory

☐ Additional information on page 2

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

Input: 220-240 V, 50/60 Hz, 0,11-0,27A; 186-250 V, 0 Hz, 0,13-0,32 A.  
Output: 0,54-1,5 A, 20-50 W  
See CB test report No.3500336.270 for complete ratings

Trademark (if any)

PHILIPS

Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

Xitanium 50W WH 0.7-1.5A 54V SR Is 230V,  
Xitanium 36W WH 0.3-1.05A 54V SR Is 230V,  
Xitanium 20W WH 0.15-0.5A 54V SR Is 230V.

Additional information (if necessary may also be reported on page 2)

☐ Additional information on page 2

A sample of the product was tested and found to be in conformity with

IEC 61347-1:2015, IEC 61347-1:2015/AMD1:2017, IEC 61347-2-13:2014, IEC 61347-2-13:2014/AMD1:2016, IEC 62384:2006, IEC 62384:2006/AMD1:2009

As shown in the Test Report Ref. No. which forms part of this Certificate

3500336.270 and 3500336.271

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.  
Meander 1051, NL-6825 MJ Arnhem, Netherlands