Ref. Certif. No.

NL-126436

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Electronic Controlgear for LED modules
Name and address of the applicant	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the manufacturer	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the factory	
When more than one factory	☒ Additional information on page 3
Ratings and principal characteristics	**Product data** Ratings: Xi FP 75W 0.2-0.7A SNLDAE 230V C133 sXt: Uin: 220-240 Vac; Iin: 0,4-0,34 Aac; Uin: 186-250 Vdc; Iin: 0,27 Adc max; fn: 50/60 Hz or DC; PF: 0,95; Pin: 84 W; Prated: 75 W; Irated: 200-700 mA; Uoutput: 50-150 Vdc, Uout: 220 Vdc max; ta: -40…+55 °C; tc: 80 °C; Built-in; Isolating. Xi FP 75W 0.3-1.0A SNLDAE 230V C133 sXt: Uin: 220-240 Vac; Iin: 0,4-0,34 Aac; Uin: 186-250 Vdc; Iin: 0,27 Adc max; fn: 50/60 Hz or DC; PF: 0,95; Pin: 84 W; Prated: 75 W; Irated: 300-1050 mA; Output voltage: 35-108 Vdc, Uout: 150 Vdc max; ta: -40…+55 °C; tc: 80 °C; Built-in; Isolating. Xi FP 75W .3-1A SNLDAE 230 C133 TR sXt: Uin: 220-240 Vac; fn: 50/60 Hz; PF: 0,95; Iin: 0,4-0,34 Aac; Pin: 84 W; Prated: 75 W; Irated: 300-1050 mA; Uoutput: 35-108 Vdc, Uout: 150 Vdc max; ta: -40…+55 °C; tc: 80 °C; Built-in; isolating. Xi FP 75W 0.5-1.5A SNLDAE 230V C133 sXt: Uin: 220-240 Vac; Iin: 0,4-0,34 Aac; Uin: 186-250 Vdc; Iin: 0,27 Adc max; fn: 50/60 Hz or DC; PF: 0,95; Pin: 84 W; Prated: 75 W; Irated: 500-1500 mA; Uoutput: 25-71 Vdc, Uout: 120 Vdc max; ta: -40…+55 °C; tc: 80 °C; Built-in; SELV

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-06-04

Signature: May Liu

DEKRA

Ref. Certif. No.

NL-126436

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

Trademark / Brand (if any)	ADVANCE, SIGNIFY, PHILIPS or XITANIUM
Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	Xi FP 75W .3-1A SNLDAE 230 C133 TR sXt, Xi FP 75W 0.2-0.7A SNLDAE 230V C133 sXt, Xi FP 75W 0.3-1.0A SNLDAE 230V C133 sXt and Xi FP 75W 0.5-1.5A SNLDAE 230V C133 sXt
Additional information	☐ Additional information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61347-1:2015, IEC 61347-1:2015/AMD1:2017, IEC 61347-2-13:2014, IEC 61347-2-13:2014/AMD1:2016 and IEC 62384:2020 National differences: EU Group Differences
As shown in the Test Report Ref. No. which forms part of this Certificate	6271277.50 and 6271277.51

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-06-04

Signature: May Liu

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

Additional factory

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-06-04

Signature: May Liu