Australia and New Zealand Certificate of Suitability- addendum

Certificate
ULL-103117-A1

Issue date
2026-06-10

Expiration date
2031-06-10

This is to acknowledge that

Signify Netherlands B.V.

High Tech Campus 48, EINDHOVEN 5656 AE
Netherlands

has had

Electronic Controlgear for LED Modules

[refer following page(s) for models list]

evaluated and meets the requirements of the standard(s)

AS 61347.2.13:2018; AS/NZS 61347.1:2016, Amd 1: 2018, Amd 2: 2025

ANZ Certification Scheme requirements.

Stuart Foster (Certification Officer)

Certification Body:
UL International New Zealand Limited,
54 Tarndale Grove, Albany, Auckland 0632, New Zealand.

Issued for use in Australia and New Zealand only.
All dates are in Year-Month-Day format (YYYY-MM-DD).

JAS-ANZ

www.jasanz.org/register

UL Solutions

© 2026 UL LLC. All rights reserved.

Australia and New Zealand
Certificate of Suitability-addendum

Certificate No: ULL-103117-A1
Original Date of Certification: 2023-09-22
Date of Issue/Revision: 2026-06-10

Trade Name or Trademark: PHILIPS, SIGNIFY, ADVANCE, XITANIUM

Risk Class / NSW Declared Class: EESS OUT OF SCOPE - Non-prescribed / non-declared

IEC Standard Country Differences: AU and NZ

Certification Marking: The RCM may be applied to the product and all the requirements of all relevant parts of AS/NZS 4417 applicable to the article shall be fulfilled.

Additional Certification Conditions: Product is a component for building in.

Model Details and Additional Information:
Xi FP 75W 0.2-0.7A SNLDAE 230V C133 sXt:
Uin: 220-240 V~, Iin: 0.4-0.34 A~, Pin: 84 W,
Uin: 186-250 Vdc, Iin: 0.27 A max dc, PF: 0.95,
fn: 50/60 Hz, DC, Pout: 75 W, Iout: 200-700 mA,
Output voltage: 50-150 Vdc, Uout(open circuit): 220 Vmax,
ta: -40…+55 °C, tc(max): 80 °C, Built-in, Isolating.

Xi FP 75W 0.3-1.0A SNLDAE 230V C133 sXt:
Uin: 220-240 V~, Iin: 0.4-0.34 A~, Pin: 84 W,
Uin: 186-250 Vdc, Iin: 0.27 A max dc, PF: 0.95,
fn: 50/60 Hz, DC, Pout: 75 W, Iout: 300-1050 mA,
Output voltage: 35-108 Vdc, Uout(open circuit): 150 Vmax,
ta: -40…+55 °C, tc: 80 °C, Built-in, Isolating.

Xi FP 75W 0.5-1.5A SNLDAE 230V C133 sXt:
Uin: 220-240 V~, Iin: 0.4-0.34 A~, Pin: 84 W,
Uin: 186-250 Vdc, Iin: 0.27 A max dc, PF: 0.95,
fn: 50/60 Hz, DC, Pout: 75 W, Iout: 500-1500 mA,
Output voltage: 25-71 Vdc, Uout(open circuit): 120 Vmax,
ta: -40…+55 °C, tc: 80 °C, Built-in, SELV

Details of addendum :
- Certificate is renewed.
- Trade names “SIGNIFY”, “XITANIUM”, and “ADVANCE” added.

© 2026 UL LLC. All rights reserved.
Form-ULID-013925-CoS - ver 2.0