



# MASTER Glass LED bulbs

## MAS LEDBulb DT3.4-40W E27 927A60CL G

MASTER, LEDbulb, A60, 40 W, E27, 2200 K, 2700 K, 470 lm, CRI 90, 25000 hour(s), Glass

Featuring a classic heritage design, these filament MASTER glass bulbs combine the familiar shapes of incandescent glass LED bulbs with the benefits of long-lasting LED technology. Ideal for creating a cozy atmosphere for customers, these glass LED bulbs provide excellent quality of light. MASTER glass bulbs can be dimmed for different lumen levels and color temperatures (dimmable glass led bulbs). They also deliver significant energy savings, using 30% less energy compared to normal LED bulbs. By offering a lifetime of 25,000 hours, these dimmable glass LED bulbs also reduce maintenance costs.

### Product data

General Information	
Cap-Base	E27
Nominal lifetime	25,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LEDbulb
Flux measurement reference	Sphere
Warranty period	5 years
Light Technical	
Color Code	922-927 [CCT of 2200K-2700K]
Luminous Flux	470 lm
Color Designation	Warm Glow(WG)
Correlated Color Temperature (Nom)	2200 2700 K

Luminous Efficacy (rated) (Nom)	138 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG0
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	3.4 W
Lamp Current (Nom)	24 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s

## MASTER Glass LED bulbs

Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.6
Voltage (Nom)	220-240 V

### Temperature

T-Case Maximum (Nom)	70 °C
----------------------	-------

### Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------

### Mechanical and Housing

Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	A60
Net Weight (Piece)	0.030 kg

### Approval and Application

Energy Efficiency Class	D
Energy Consumption kWh/1000 h	4 kWh
EPREL Registration Number	1109129
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes

Flickering value (PstLM) - Flickering value as per EN 61000-3-3	0.9
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 °C to 45 °C


### Application Conditions

can it be used in closed luminaires	No
Wireless Technology	Not applicable

### Product Data

Order product name	MAS LEDBulb DT3.4-40W E27 927A60CL G
Full product name	MAS LEDBulb DT3.4-40W E27 927A60CL G
Full product code	871951444967100
Order code	929003009982
Material Nr. (12NC)	929003009982
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514449671
Numerator - Packs per outer box	10
EAN/UPC - Case	8719514449688



## Dimensional drawing



Product	D	C
MAS LEDBulb DT3.4-40W E27 927A60CL G	60 mm	104 mm


# MASTER Glass LED bulbs

## Photometric data




Spectral Power Distribution Colour - MAS LEDBulb DT3.4-40W E27 927A60CL G

Light Distribution Diagram - MAS LEDBulb DT3.4-40W E27 927A60CL G



General uniform lighting - MAS LEDBulb DT3.4-40W E27 927A60CL G

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - MAS LEDBulb DT3.4-40W E27 927A60CL G

## MASTER Glass LED bulbs

