



# MASTER Glass LED bulbs

## MAS LEDBulb DT7.2-75W E27 927 A60 FR G

MASTER, LEDbulb, A60, 75 W, E27, 2200 K, 2700 K, 1055 lm, CRI 90, 25000 hour(s)

Featuring a classic heritage design, these filament MASTER glass bulbs combine the familiar shapes of incandescent glass LED bulbs with the benefits of long-lasting LED technology. Ideal for creating a cozy atmosphere for customers, these glass LED bulbs provide excellent quality of light. MASTER glass bulbs can be dimmed for different lumen levels and color temperatures (dimmable glass led bulbs). They also deliver significant energy savings, using 30% less energy compared to normal LED bulbs. By offering a lifetime of 25,000 hours, these dimmable glass LED bulbs also reduce maintenance costs.

### Product data

General Information		Luminous Efficacy (rated) (Nom)	
Cap-Base	E27		146.00 lm/W
Nominal lifetime	25,000 hour(s)	Color Consistency	<6
Switching Cycle	20,000	Color rendering index (CRI)	90
Lighting Technology	LEDbulb	LLMF At End Of Nominal Lifetime (Nom)	70 %
Flux measurement reference	Sphere	Photobiological safety according to EN 62471	RG0
Warranty period	5 years		
Light Technical		Operating and Electrical	
Color Code	922-927 [CCT of 2200K-2700K]	Line Frequency	50 to 60 Hz
Luminous Flux	1,055 lm	Input Frequency	50 to 60 Hz
Color Designation	Warm Glow(WG)	Power Consumption	7.2 W
Correlated Color Temperature (Nom)	2200 2700 K	Lamp Current (Nom)	49 mA
		Wattage Equivalent	75 W
		Starting Time (Nom)	0.5 s

# MASTER Glass LED bulbs

Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.6
Voltage (Nom)	220-240 V

## Temperature

T-Case Maximum (Nom)	70 °C
----------------------	-------

## Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------

## Mechanical and Housing

Bulb Finish	Frosted
Bulb Shape	A60
Net Weight (Piece)	0.030 kg

## Approval and Application

Energy Efficiency Class	D
Energy Consumption kWh/1000 h	8 kWh
EPREL Registration Number	453256
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes

Flickering value (PstLM) - Flickering value as per EN 61000-3-3	0.9
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 to +45 °C


## Application Conditions

can it be used in closed luminaires	No
-------------------------------------	----

## Product Data



Order product name	MAS LEDBulb DT7.2-75W E27 927 A60 FR G
Full product name	MAS LEDBulb DT7.2-75W E27 927 A60 FR G
Full product code	871951432493000
Order code	929003011302
Material Nr. (12NC)	929003011302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514324930
Numerator - Packs per outer box	10
EAN/UPC - Case	8719514324947

## Dimensional drawing



Product	D	C
MAS LEDBulb DT7.2-75W E27 927 A60 FR G	60 mm	104 mm

## Photometric data




Light Distribution Diagram - MAS LEDBulb DT7.2-75W E27 927 A60 FR G

General uniform lighting - MAS LEDBulb DT7.2-75W E27 927 A60 FR G

# MASTER Glass LED bulbs

## Photometric data



Spectral Power Distribution Colour - MAS LEDBulb DT7.2-75W E27 927 A60 FR G

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - MAS LEDBulb DT7.2-75W E27 927 A60 FR G

