



MASTER LED spot LV

MASTER LED 6.5-50W 940 MR16 36D Dim

LEDspot, MR16, 50 W, GU5.3, 4000 K, 530 lm, 40000 hour(s)

Delivering intense accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot lighting. MASTER LEDspot LV is designed to replace halogen or incandescent spots. It realizes natural colors, enables cozy and comfortable ambience for residential, hospitality and emphasizes the beauty of merchandise in retail. New smaller housing provides perfect fitting with majority of luminaires in a market with a MR16 GU 5.3 holder. It not only employs Philips' patented solution to guarantee the broadest possible compatibility with standard 12V halogen electronic transformers, it also delivers high beam intensity which is equivalent to halogen MR16 spots. The dimming function enables to create the desired atmosphere and it works with broad selection of dimmers. Its high SDCM ensure stricter color consistency, that is maintained over product life. MASTER LEDspot LV delivers huge energy savings and minimizes maintenance cost without any compromise on light quality and lifetime, enabling residential and business owners to achieve a return on their investment within short period time.

Product data

General Information		Luminous Intensity (Nom)	
Cap-Base	GU5.3		1,600 cd
Nominal lifetime	40,000 hour(s)	Color Designation	Cool White (CW)
Switching Cycle	50,000	Correlated Color Temperature (Nom)	4000 K
Lighting Technology	LEDspot	Luminous Efficacy (rated) (Nom)	81.00 lm/W
Warranty period	3 years	Color Consistency	<4
		Color rendering index (CRI)	90
		LLMF At End Of Nominal Lifetime (Nom)	70 %
Light Technical		Operating and Electrical	
Color Code	940 [CCT of 4000K]	Line Frequency	- Hz
Beam Angle (Nom)	36 degree(s)	Input Frequency	- Hz
Luminous Flux	530 lm		

MASTER LED spot LV

Power Consumption	6.5 W
Lamp Current (Nom)	650 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	ac electronic 12 V

Temperature

T-Case Maximum (Nom)	90 °C
----------------------	-------


Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------


Mechanical and Housing

Bulb Shape	MR16
Net Weight (Piece)	0.060 kg

Dimensional drawing



Photometric data



Light Distribution Diagram - MASTER LED 6.5-50W 940 MR16 36D Dim


Approval and Application

Suitable For Accent Lighting	Yes
EU RoHS compliant	Yes
Ambient temperature range	-20 to +45 °C

Product Data

Order product name	MASTER LED 6.5-50W 940 MR16 36D Dim
Full product name	MASTER LED 6.5-50W 940 MR16 36D Dim
Full product code	871951435795200
Order code	929003072408
Material Nr. (12NC)	929003072408
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514357952
Numerator - Packs per outer box	10
EAN/UPC - Case	8719514357969


Product	D	C
MASTER LED 6.5-50W 940 MR16 36D Dim	50 mm	46.5 mm



Accent Lighting Spots - MASTER LED 6.5-50W 940 MR16 36D Dim

MASTER LED spot LV

Photometric data



Spectral Power Distribution Colour - MASTER LED 6.5-50W 940 MR16 36D Dim

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - MASTER LED 6.5-50W 940 MR16 36D Dim

