

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME**CB TEST CERTIFICATE**

Product	Electronic Controlgear for LED modules
Name and address of the applicant	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the manufacturer	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the factory	
<i>When more than one factory</i>	<input checked="" type="checkbox"/> Additional information on page 2
Ratings and principal characteristics	Product data Ratings: Uin: 220-240 V; fn: 50/60 Hz; lin: 0,44 A max; Uin: 186-250 V dc; lin: 0,52 A dc max; Prated: 90 W max; Irated: 0,08-0,7 Adc; Uoutput: 50-300 Vdc, Uout: 330V dc max; tc: 80°C max; ta: -25...+50 °C; PF: 0,99; built-in; EL
Trademark / Brand (if any)	PHILIPS or SIGNIFY
Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	Xitanium pW x-yA nV SR mV Gi
Additional information	<input checked="" type="checkbox"/> Additional information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61347-1:2015, IEC 61347-1:2015/AMD1:2017, IEC 61347-2-13:2014, IEC 61347-2-13:2014/AMD1:2016 and IEC 62384:2020 National differences: EU Group Differences
As shown in the Test Report Ref. No. which forms part of this Certificate	6231292.50 and 6231292.51

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2025-06-30

Signature: Kreny Lin

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

Additional factory

Additional information

Note:

Xitanium pW x-yA nV SR mV Gi

p= Rated output power in watt, maximum to 90, step per 5.

x= Minimum adjustable output current in ampere by simple set, from 0,08 to 0,25, step per 0,01.

y= Maximum adjustable output current in ampere by simple set, from 0,35 to 0,7, step per 0,01.

n= Rated output voltage in volt, maximum to 300.

m= Rated input voltage in volt.

i= Version control number of LED driver for commercial purpose, starting from 2.

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands



Date: 2025-06-30

Signature: Kreny Lin