Australia and New Zealand Certificate of Suitability-addendum

Certificate
ULL-102769-A1

Issue date
2026-06-02

Expiration date
2031-06-02

This is to acknowledge that

Signify Netherlands B.V.

High Tech Campus 48, EINDHOVEN 5656 AE
Netherlands

has had

LED Driver {component for building-in}

[refer following page(s) for models list]

evaluated and meets the requirements of the standard(s)

AS 61347.2.13:2018; AS/NZS 61347.1:2016, Amd 1: 2018, Amd 2: 2025

ANZ Certification Scheme requirements.

Stuart Foster (Certification Officer)

Certification Body:
UL International New Zealand Limited,
54 Tarndale Grove, Albany, Auckland 0632, New Zealand.

Issued for use in Australia and New Zealand only.
All dates are in Year-Month-Day format (YYYY-MM-DD).

JAS-ANZ

www.jasanz.org/register

UL Solutions

© 2026 UL LLC. All rights reserved.

Australia and New Zealand
Certificate of Suitability-addendum

Certificate No: ULL-102769-A1
Original Date of Certification: 2022-11-23
Date of Issue/Revision: 2026-06-02

Trade Name or Trademark: PHILIPS, XITANIUM, SIGNIFY, ADVANCE

Risk Class / NSW Declared Class: EESS OUT OF SCOPE - Non-prescribed / non-declared

IEC Standard Country Differences: AU and NZ

Certification Marking: The RCM may be applied to the product and all the requirements of all relevant parts of AS/NZS 4417 applicable to the article shall be fulfilled.

Additional Certification Conditions: Product is a component for building in.

Model Details and Additional Information:
Rating Information:
Xitanium 90W 0.25-0.7A 220V SR 230V G2
Uin: 220-240 V~, fn: 50/60 Hz, Iin: 0.44 A~ max,
Uin: 186-250 Vdc, Iin: 0.52 Adc max,
Pout: 90 W max, Iout: 0.25-0.7 Adc,
Output Voltage(range): 50-220 Vdc, Uout: 250 Vdc max,
tc: 80°C max, ta: -25…+50 °C, PF: 0.99, built-in

Xitanium 60W 0.08-0.35A 300V SR 230V G2
Uin: 220-240 V~, fn: 50/60 Hz, Iin: 0.30 A~ max,
Uin: 186-250 Vdc, Iin: 0.36 Adc max,
Pout: 60 W max, Iout: 0.08-0.35 Adc,
Output Voltage(range): 100-300 Vdc, Uout: 330 Vdc max,
tc: 75°C max, ta: -25…+50 °C, PF: 0.99, built-in

Xitanium 60W 0.15-0.5A 220V SR 230V G2
Uin: 220-240 V~, fn: 50/60 Hz, Iin: 0.30 A~ max,
Uin: 186-250 Vdc, Iin: 0.36 Adc max,
Pout: 60 W max, Iout: 0.15-0.5 Adc,
Output Voltage(range): 50-220 Vdc, Uout: 250 Vdc max,
tc: 75°C max, ta: -25…+50 °C, PF: 0.99, built-in

Xitanium 35W 0.08-0.35A 220V SR 230V G2
Uin: 220-240 V~, fn: 50/60 Hz, Iin: 0.18 A~ max,
Uin: 186-250 Vdc, Iin: 0.21 Adc max,
Pout: 35 W max, Iout: 0.08-0.35 Adc,
Output Voltage(range): 50-220 Vdc, Uout: 250 Vdc max,
tc: 75°C max, ta: -25…+50 °C, PF: 0.99, built-in

General Information:
The LED driver has non-isolated output and is designed to be used for Class I luminaires at ambient temperature of 50°C (+/-5°C).
SELV output for Dali circuit.

Details of addendum :
- Certificate is renewed.
- Trade names “SIGNIFY”, “XITANIUM”, and “ADVANCE” added.

© 2026 UL LLC. All rights reserved.