

12345678910

A

Dimensions and weight



Specification item	Value	Unit	Condition
Length (A1)	204 ± 0.5	mm	
Width (B1)	30 ± 0.5	mm	
Height (C1)	21 ± 0.4	mm	
Fixing hole diameter	3.5	mm	
Fixing hole distance (A2)	193.5 ± 0.2	mm	
Fixing hole distance (B2)	N.A.	mm	
Weight	93.7	gram	

B

C

W

D



E

F

G


F

H

TLD	
HID	

12345678910

Philips (China) Investment Co., Ltd.
All rights are reserved. Reproduction in whole or in part is
prohibited without the written consent of the copyright owner.

GB/T 1804-2000m (Unit: mm)												
SIZE RANGE	0.5-3	>3-6	>6-30	>30-120	>120-400	>400-1000						
TOLERANCE	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8	ITEM	ASSEMBLY NO.	QUANT.			
GENERAL ROUGHNESS	UNIT	MATERIAL						MODEL				
✓	mm											
SCALE	PROJECT TYPE	TREATMENT						ORDER NO.	QUANT.			
												
		MODEL NAME: Xitanium SR Bridge Build-in				WEIGHT: (g)	PART NUMBER: 9290 034 23700		2022-09-19 A			
REV. CHANGE NO.		DATE										
DESIGNED BY		G.Sun	CHECKED BY		1	SH.	SH. 112 of 1		FORM NO.	A3		
DRAWN BY			APPROVED BY		REVISED BY		Philips (China) Investment Co., Ltd.					