

CERTIFICATE

Issued to:
Applicant:
Signify Netherlands B.V.
High Tech Campus 48
5656 AE Eindhoven, Netherlands

Licensee:
Signify Netherlands B.V.
High Tech Campus 48
5656 AE Eindhoven, Netherlands

Product : Controller
Trade name(s) : ADVANCE, PHILIPS, SIGNIFY or XITANIUM
Type(s)/model(s) : Xitanium SR Bridge 9290015464, Xitanium SR Bridge 9290015465,
Xitanium SR Bridge Built-in and Xitanium SR Bridge Independent

The product and any acceptable variation thereof as specified in the Annex to this certificate and the documents referred to therein.

DEKRA hereby declares that the above-mentioned product has been certified based on:

- a type test according to EN 61347-2-11:2001, EN 61347-2-11:2001/A1:2019, EN 61347-1:2015 and EN 61347-1:2015/A1:2021
- an inspection of the factory location according to CENELEC Operational Document CIG 421
- a DEKRA certification agreement with the number 947556

DEKRA hereby grants the right to use the ENEC certification mark.


The ENEC certification mark may be applied to the product as specified in this certificate for the duration and under the conditions of the ENEC certification agreement.

This licence has been issued under the presumption and conditional on the fact that the licensee holds all necessary legal rights with regard to the product presented for testing and certification.

This certificate is issued on 7 July 2026 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 31-178579

DEKRA Certification B.V.



B.T.M. Holtus
Managing Director



Kreny Lin
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL



SPECIFICATION OF THE CERTIFIED PRODUCT**Product data**

Product	: Controller
Trade name(s)	: ADVANCE, PHILIPS, SIGNIFY or XITANIUM
Type(s)/model(s)	: Xitanium SR Bridge 9290015464, Xitanium SR Bridge 9290015465, Xitanium SR Bridge Built-in and Xitanium SR Bridge Independent
Rated input voltage	: 220-240 Vac
Rated frequency	: 50/60 Hz
Rated input current	: 12-20 mA
Rated input power	: 0,3-2,0 W (no load)
Rated loaded power	: 400 VA max.
Ambient temperature range (ta)	: -40...+60 °C
Max.case temperature (tc)	: 75 °C
Description	: see product data per type

Product data – type Xitanium SR Bridge 9290015465 and Xitanium SR Bridge Independent

Description	: independent
-------------	---------------

Product data – type Xitanium SR Bridge 9290015464 and Xitanium SR Bridge Built-in

Description	: Built-in
-------------	------------

TESTS**Test requirements**

EN 61347-2-11:2001
EN 61347-2-11:2001/A1:2019
EN 61347-1:2015
EN 61347-1:2015/A1:2021

Test result

The test results are documented in DEKRA test file 6271393.50(A-B).

Additional information

with screwless terminal

Thermal protected

The insulation between LV and SR terminal is considered as basic insulation.

The insulation between LV and DALI terminal is considered as double/reinforced insulation

The tests were performed by the manufacturer under the conditions of the agreement concerning the manufacturer's right to conduct type tests for the ENEC certification system under supervision of DEKRA (CTF Stage 3).

The list of components is laid down in test report 6271393.50.

Conclusion

The examination has confirmed that all requirements were met.

Factory location

The factory location is registered with the number 305810.