CERTIFICATE

Issued to:
Applicant:
Signify Netherlands B.V.
High Tech Campus 48
5656 AE Eindhoven, Netherlands

Licensee:
Signify Netherlands B.V.
High Tech Campus 48
5656 AE Eindhoven, Netherlands

Product	:	Lighting Controller/Sensor
Trade name(s)	:	PHILIPS or SIGNIFY
Type(s)/model(s)	:	EasyAir SNM212/g MC and EasyAir SNM212/w MC

The product and any acceptable variation thereof as specified in the Annex to this certificate and the documents referred to therein.

DEKRA hereby declares that the above-mentioned product has been certified based on:
- a type test according to EN 61347-2-11:2001, EN 61347-2-11:2001/A1:2019, EN 61347-1:2015 and EN 61347-1:2015/A1:2021
- an inspection of the factory location according to CENELEC Operational Document CIG 021
- a DEKRA certification agreement with the number 947556

DEKRA hereby grants the right to use the ENEC certification mark.

The ENEC certification mark may be applied to the product as specified in this certificate for the duration and under the conditions of the ENEC certification agreement.

This certificate is issued on 15 September 2025 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 31-164702

DEKRA Certification B.V.

B.T.M. Holtus
Managing Director

Kate Xu
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL

PRODUCTS
RvA C 001

DEKRA Certification B.V. Meander 1051, 6825 MJ Arnhem P.O. Box 5185, 6802 ED Arnhem, Netherlands
T +31 88 96 83000 F +31 88 96 83100 www.dekra.nl Company registration 09085396

SPECIFICATION OF THE CERTIFIED PRODUCT

Product data

Product	:	Lighting Controller/Sensor
Trade name(s)	:	PHILIPS or SIGNIFY
Type(s)/model(s)	:	EasyAir SNM212/g MC and EasyAir SNM212/w MC
Rated voltage (Uin)	:	9,5-22,5 Vdc
Rated current (Iin)	:	9,5 mA
Rated power (Pin)	:	140 mW
Ambient temperature (ta)	:	-30…+55 °C
Max. case temperature (tc)	:	max 60 °C
Description	:	IP66; Class II

TESTS

Test requirements

EN 61347-2-11:2001
EN 61347-2-11:2001/A1:2019
EN 61347-1:2015
EN 61347-1:2015/A1:2021

Test result

The test results are documented in DEKRA test file 6236232.50(A-B).

Additional information

The tests were performed by the manufacturer under the conditions of the agreement concerning the manufacturer's right to conduct type tests for the ENEC certification system under supervision of DEKRA (CTF Stage 3).

The list of components is laid down in test report 6236232.50A.

Conclusion

The examination has confirmed that all requirements were met.

Factory locations

The factory locations are registered with the numbers 674666 and 305810.