

# CERTIFICATE

Issued to:  
Applicant:  
**Signify Netherlands B.V.**  
**High Tech Campus 48**  
**5656 AE Eindhoven, Netherlands**

Licensee:  
**Signify Netherlands B.V.**  
**High Tech Campus 48**  
**5656 AE Eindhoven, Netherlands**

Product : Electronic Controlgear for LED modules  
Trade name(s) : PHILIPS or SIGNIFY  
Type(s)/model(s) : Xitanium 65W 175-350mA 185V DS 230V

The product and any acceptable variation thereof as specified in the Annex to this certificate and the documents referred to therein.

DEKRA hereby declares that the above-mentioned product has been certified based on:

- a type test according to EN 61347-2-13:2014, EN 61347-2-13:2014/A1:2017, EN 61347-1:2015, EN 61347-1:2015/A1:2021 and EN IEC 62384:2020
- an inspection of the factory location according to CENELEC Operational Document CIG 021
- a DEKRA certification agreement with the number 947556


DEKRA hereby grants the right to use the ENEC certification mark.

The ENEC certification mark may be applied to the product as specified in this certificate for the duration and under the conditions of the ENEC certification agreement.

This certificate is issued on 7 July 2025 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 31-130826 REV.2

DEKRA Certification B.V.



B.T.M. Holtus  
Managing Director



Kreny Lin  
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE  
DUTCH ACCREDITATION  
COUNCIL



**SPECIFICATION OF THE CERTIFIED PRODUCT****Product data**

Product	: Electronic Controlgear for LED modules
Trade name(s)	: PHILIPS or SIGNIFY
Type(s)/model(s)	: Xitanium 65W 175-350mA 185V DS 230V
Input voltage	: 220-240 Vac
Frequency	: 50/60Hz
Power factor (PF)	: 0,95
Input current	: 0,33-0,16 Aac
Input power	: 71 W
Output voltage	: 120-185 Vdc
Max working voltage (Uout)	: 250 V
Output current	: 0,175/0,25/0,3/0,35 A
Output power	: 32,4/46,3/55,5/65 W
Case temperature (tc)	: 85 °C
Ambient temperature (ta)	: -20...+50°C
Temperature declared thermally protection	: 110 °C
Description	: Built-in

**TESTS****Test requirements**

EN 61347-2-13:2014  
EN 61347-2-13:2014/A1:2017  
EN 61347-1:2015  
EN 61347-1:2015/A1:2021  
EN IEC 62384:2020

**Test result**

The test results are documented in DEKRA test file 6231291.50 and 6231291.51.

**Additional information**

This certificate replaces certificate No. 31-130826 REV.1 which we hereby declare invalid.

The list of components is laid down in test report 6231291.50.

**Conclusion**

The examination has confirmed that all requirements were met.

**Factory locations**

The factory locations are registered with the numbers 674666 and 306303.