



MASTER LED tube T8 UltraEfficient with Recycled Plastic

MAS LEDtube 1500mm UE 17.6W 840 T8 EELA

MASTER, LEDtube, T8, EM/Mains, 1500 mm, 17.6 W, 58W TL-D, 4000 K, 3700 lm, CRI 80, 100000 hour(s)

MASTER, LEDtube, T8, EM/Mains, 1500 mm, 17.6 W, LED alternative to 58W TL-D, 4000 K, 3700 lm, CRI 80, 100000 hour(s), 210 lm/W, EEL A, G13 Rotatable end-cap, Beam angle 160 degree(s), Plastic, 40 %, 1500 mm, RGO, SDCM 6, PF 0.9, IP20, SVM 0.1, PstLM 0.1

Product data

General Information		Operating and Electrical	
Cap-Base	G13 Rotatable end-cap	Luminous Efficacy (rated) (Nom)	210 lm/W
Nominal lifetime	100,000 hour(s)	Color Consistency	<6
Switching Cycle	200,000	Color rendering index (CRI)	80
Lighting Technology	LEDtube	LLMF At End Of Nominal Lifetime (Nom)	70 %
Flux measurement reference	Sphere	Photobiological safety according to EN 62471	RGO
Warranty period	10 years		
Light Technical		Line Frequency	50 to 60 Hz
Color Code	840 [CCT of 4000K]	Input Frequency	50 to 60 Hz
Beam Angle (Nom)	160 degree(s)	Power Consumption	17.6 W
Luminous Flux	3,700 lm	Lamp Current (Max)	93 mA
Color Designation	Cool White (CW)	Lamp Current (Min)	73 mA
Correlated Color Temperature (Nom)	4000 K	Starting Time (Nom)	0.5 s
		Warm-up time to 60% light	0.5 s

MASTER LED tube T8 UltraEfficient with Recycled Plastic

Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
LED alternative to fluorescent lamp power	58W TL-D
Inrush current at mains	5
Max. lamp no. on MCB B type 10A – Mains	80
Max. lamp no. on MCB B type 10A – EM ballast without Compensation Capacitor.	80
Max. lamp no. on MCB B type 10A – EM ballast with Compensation Capacitor.	10
Max. lamp no. on MCB B type 16A – Mains	130
Max. lamp no. on MCB B type 16A – EM ballast without Compensation Capacitor.	130
Max. lamp no. on MCB B type 16A – EM ballast with Compensation Capacitor.	16
Ballast Compatibility	EM/Mains

Temperature

T-Case Maximum (Nom)	45 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Plastic
Product Length	1,500 mm
Bulb Shape	T8
Net Weight (Piece)	0.285 kg

Approval and Application

Energy Efficiency Class	A
Energy Saving Product	Yes
Approval Marks	RoHS compliance CE marking KEMA Keur certificate ENEC certificate

Energy Consumption kWh/1000 h	18 kWh
EPREL Registration Number	2102397
CE mark	Yes
EU RoHS compliant	Yes
LED Innovations	UltraEfficient
Flickering value (PstLM) – Flickering value as per EN 61000-3-3	0.1
Stroboscopic effect visibility measure (SVM)	0.1
Ambient temperature range	-20 to +45 °C
Post-consumer recycled plastic material ratio	40 %

Application Conditions

can it be used in closed luminaires	Yes
Wireless Technology	Not applicable


Sustainability Data

Sustainability rating	Signify Circle
Product non-virgin material ratio	25.3 %

Product Data

Order product name	MAS LEDtube 1500mm UE 17.6W 840 T8 EELA
Full product name	MAS LEDtube 1500mm UE 17.6W 840 T8 EELA
Full product code	871951443168300
Order code	929003482302
Material Nr. (12NC)	929003482302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514431683
Numerator - Packs per outer box	10
EAN/UPC - Case	8719514431690



Dimensional drawing



Product	D1	D2	A1	A2	A3
MAS LEDtube 1500mm UE 17.6W 840 T8 EELA	25.8 mm	28 mm	1,498.8 mm	1,505.9 mm	1,513 mm


MASTER LED tube T8 UltraEfficient with Recycled Plastic

Photometric data




General uniform lighting - MAS LEDtube 1500mm UE 17.6W 840 T8 EELA

Light Distribution Diagram - MAS LEDtube 1500mm UE 17.6W 840 T8 EELA




Spectral Power Distribution Colour - MAS LEDtube 1500mm UE 17.6W 840 T8 EELA

Lifetime





Life Expectancy Diagram



Lumen Maintenance Diagram - MAS LEDtube 1500mm UE 17.6W 840 T8 EELA


MASTER LED tube T8 UltraEfficient with Recycled Plastic

Lifetime



LifetimeVsTc

LEDtube-100K-4565-FailureRate-LED



Lumen Maintenance Diagram - MAS LEDtube 1500mm UE 17.6W 840 T8 EELA

