



# MASTER VALUE LED spot PAR



## MAS LEDspot VLE D 6-50W 927 PAR20 25D

MASTER Value, LEDspot, PAR20, 50 W, E27, 2700 K, 500 lm, CRI 90, 25000 hour(s), Glass

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. It's a dimmable solution. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. The product offers more energy saving comparing with normal LED spots.

### Product data

General Information	
Cap-Base	E27
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot
Flux measurement reference	Narrow Cone
Warranty period	5 years
Light Technical	
Color Code	927 [CCT of 2700K]
Beam Angle (Nom)	25 degree(s)
Luminous Flux	500 lm
Luminous Intensity (Nom)	1,500 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	83 lm/W

Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	500 lm
Photobiological safety according to EN 62471	RG1


Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	6 W
Lamp Current (Nom)	40 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7

# MASTER VALUE LED spot PAR

Voltage (Nom)	220-240 V
<b>Temperature</b>	
T-Case Maximum (Nom)	80 °C
<b>Controls and Dimming</b>	
Dimmable	Only with specific dimmers
<b>Mechanical and Housing</b>	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	PAR20
Net Weight (Piece)	0.080 kg
<b>Approval and Application</b>	
Energy Efficiency Class	F
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	6 kWh
EPREL Registration Number	1121750
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1

Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 to +45 °C
<b>Application Conditions</b>	
can it be used in closed luminaires	No
Wireless Technology	Not applicable
<b>Product Data</b>	
Order product name	MAS LEDspot VLE D 6-50W 927 PAR20 25D
Full product name	MAS LEDspot VLE D 6-50W 927 PAR20 25D
Full product code	871951444304400
Order code	929003485702
Material Nr. (12NC)	929003485702
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514443044
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514443051



## Dimensional drawing



Product	D	C
MAS LEDspot VLE D 6-50W 927 PAR20 25D	65 mm	85 mm


# MASTER VALUE LED spot PAR

## Photometric data




Accent Lighting Spots - MAS LEDspot VLE D 6-50W 927 PAR20 25D

Spectral Power Distribution Colour - MAS LEDspot VLE D 6-50W 927 PAR20 25D




Light Distribution Diagram - MAS LEDspot VLE D 6-50W 927 PAR20 25D

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - MAS LEDspot VLE D 6-50W 927 PAR20 25D

## MASTER VALUE LED spot PAR

