



# CorePro Plastic LED bulbs

## CoreProLEDbulb ND 4.9-40W A60 E27 927

CorePro, LEDbulb, A60, 40 W, E27, 2700 K, 470 lm, CRI 90, 15000 hour(s), Plastic

The CorePro LED bulb is the perfect bulb for your basic lighting needs. It provides beautiful light and dependable performance you expect from LED at an affordable price. CorePro LEDbulbs are compatible with existing fixtures with an E27 or B22 holder and are designed for retrofit replacement of incandescent bulbs. They deliver huge energy savings of 80% and provides excellent quality of light. By offering a lifetime of 15,000 hours it reduces maintenance costs.

### Product data


General Information		Color Consistency	
Cap-Base	E27	Color Consistency	<6
Nominal lifetime	15,000 hour(s)	Color rendering index (CRI)	90
Switching Cycle	50,000	LLMF At End Of Nominal Lifetime (Nom)	70 %
Lighting Technology	LEDbulb	Photobiological safety according to EN 62471	RG0
Flux measurement reference	Sphere	Operating and Electrical	
Warranty period	2 years	Line Frequency	50 Hz
Light Technical		Input Frequency	50 Hz
Color Code	927 [CCT of 2700K]	Power Consumption	4.9 W
Beam Angle (Nom)	180 degree(s)	Lamp Current (Nom)	45 mA
Luminous Flux	470 lm	Wattage Equivalent	40 W
Color Designation	Warm White (WW)	Starting Time (Nom)	0.5 s
Correlated Color Temperature (Nom)	2700 K	Warm-up time to 60% light	0.5 s
Luminous Efficacy (rated) (Nom)	95 lm/W	Power Factor (Fraction)	0.4

## CorePro Plastic LED bulbs

Voltage (Nom)	220-240 V
<b>Temperature</b>	
T-Case Maximum (Nom)	80 °C
<b>Controls and Dimming</b>	
Dimmable	No
<b>Mechanical and Housing</b>	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A60
Net Weight (Piece)	0.025 kg
<b>Approval and Application</b>	
Energy Efficiency Class	F
Energy Consumption kWh/1000 h	5 kWh
EPREL Registration Number	1211087
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM) - Flickering value as per 1 EN 61000-3-3	

Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 °C to 45 °C
<b>Application Conditions</b>	
can it be used in closed luminaires	No
<b>Product Data</b>	
Order product name	CoreProLEDbulb ND 4.9-40W A60 E27 927
Full product name	CoreProLEDbulb ND 4.9-40W A60 E27 927
Full product code	871951447518200
Order code	929003542502
Material Nr. (12NC)	929003542502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514475182
Numerator - Packs per outer box	10
EAN/UPC - Case	8719514475199


### Dimensional drawing




Product	D	C
CoreProLEDbulb ND 4.9-40W A60 E27 927	60 mm	107 mm

# CorePro Plastic LED bulbs


## Photometric data



General uniform lighting - CoreProLEDbulb ND 4.9-40W A60 E27 927



Spectral Power Distribution Colour - CoreProLEDbulb ND 4.9-40W A60 E27 927




Light Distribution Diagram - CoreProLEDbulb ND 4.9-40W A60 E27 927

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - CoreProLEDbulb ND 4.9-40W A60 E27 927

## CorePro Plastic LED bulbs

