



Classic LED spotMV

LEDClassic 2.1W GU10 WH 36D ND UE SRT6

LEDspot, PAR16, 50 W, GU10, 3000 K, 400 lm, 50000 hour(s), Glass

LEDspot, PAR16, 50 W, GU10, 3000 K, 400 lm, 50000 hour(s), Glass, 190 lm/W

Product data

General Information		Wattage Equivalent	
Cap-Base	GU10		50 W
Nominal lifetime	50,000 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	50,000	Warm-up time to 60% light	0.5 s
Lighting Technology	LEDspot	Power Factor (Fraction)	0.3
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	830 [CCT of 3000K]	T-Case Maximum (Nom)	60 °C
Beam Angle (Nom)	36 degree(s)		
Luminous Flux	400 lm	Controls and Dimming	
Luminous Intensity (Nom)	680 cd	Dimmable	No
Color Designation	White (WH)		
Correlated Color Temperature (Nom)	3000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	190 lm/W	Bulb Finish	Clear
Color Consistency	<6	Bulb Material	Glass
Color rendering index (CRI)	80	Overall length	54 mm
LLMF At End Of Nominal Lifetime (Nom)	70 %	Overall width	50 mm
		Overall height	54 mm
		Dimensions (Height x Width x Depth)	54 x 50 x 54 mm
		Bulb Shape	PAR16
		Net Weight (Piece)	0.044 kg
Operating and Electrical			
Input Frequency	50 to 60 Hz		
Power Consumption	2.1 W		
Lamp Current (Nom)	31 mA		

Classic LED spotMV

Approval and Application

Suitable For Accent Lighting	Yes
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	UltraEfficient
Ambient temperature range	-20 to +45 °C

Application Conditions


Wireless Technology	Not applicable
---------------------	----------------

Product Data

Order product name	LEDClassic 2.1W GU10 WH 36D ND UE SRT6
--------------------	--


Full product name	LEDClassic 2.1W GU10 WH 36D ND UE SRT6
Full product code	872110304284200
Order code	929003610019
Material Nr. (12NC)	929003610019
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103042842
Numerator - Packs per outer box	6
EAN/UPC - Case	8721103042859

Dimensional drawing




Product	D	C
LEDClassic 2.1W GU10 WH 36D ND UE SRT6	50 mm	54 mm

Photometric data




Light Distribution Diagram - LEDClassic 2.1W GU10 WH 36D ND UE SRT6



Spectral Power Distribution Colour - LEDClassic 2.1W GU10 WH 36D ND UE SRT6

Classic LED spotMV

Photometric data



Accent Lighting Spots - LEDClassic 2.1W GU10 WH 36D ND UE SRT6

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDClassic 2.1W GU10 WH 36D ND UE SRT6

