



# Classic LED spotMV

## LEDClassic 2.1W GU10 CW 36D ND UE SRT6

LEDspot, PAR16, 50 W, GU10, 4000 K, 400 lm, 50000 hour(s), Glass

LEDspot, PAR16, 50 W, GU10, 4000 K, 400 lm, 50000 hour(s), Glass, 190 lm/W

### Product data

General Information		Wattage Equivalent	
Cap-Base	GU10		50 W
Nominal lifetime	50,000 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	50,000	Warm-up time to 60% light	0.5 s
Lighting Technology	LEDspot	Power Factor (Fraction)	0.3
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	840 [CCT of 4000K]	T-Case Maximum (Nom)	60 °C
Beam Angle (Nom)	36 degree(s)		
Luminous Flux	400 lm	Controls and Dimming	
Luminous Intensity (Nom)	680 cd	Dimmable	No
Color Designation	Cool White (CW)	Mechanical and Housing	
Correlated Color Temperature (Nom)	4000 K	Bulb Finish	Clear
Luminous Efficacy (rated) (Nom)	190 lm/W	Bulb Material	Glass
Color Consistency	<6	Overall length	54 mm
Color rendering index (CRI)	80	Overall width	50 mm
LLMF At End Of Nominal Lifetime (Nom)	70 %	Overall height	54 mm
		Dimensions (Height x Width x Depth)	54 x 50 x 54 mm
Operating and Electrical		Bulb Shape	PAR16
Input Frequency	50 to 60 Hz	Net Weight (Piece)	0.044 kg
Power Consumption	2.1 W		
Lamp Current (Nom)	31 mA		

# Classic LED spotMV

## Approval and Application

Suitable For Accent Lighting	Yes
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	UltraEfficient
Ambient temperature range	-20 to +45 °C

## Application Conditions


Wireless Technology	Not applicable
---------------------	----------------

## Product Data

Order product name	LEDClassic 2.1W GU10 CW 36D ND UE SRT6
--------------------	--



Full product name	LEDClassic 2.1W GU10 CW 36D ND UE SRT6
Full product code	872110304249100
Order code	929003610119
Material Nr. (12NC)	929003610119
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103042491
Numerator - Packs per outer box	6
EAN/UPC - Case	8721103042507

## Dimensional drawing



Product	D	C
LEDClassic 2.1W GU10 CW 36D ND UE SRT6	50 mm	54 mm

## Photometric data




Accent Lighting Spots - LEDClassic 2.1W GU10 CW 36D ND UE SRT6

Spectral Power Distribution Colour - LEDClassic 2.1W GU10 CW 36D ND UE SRT6

# Classic LED spotMV

## Photometric data



Light Distribution Diagram - LEDClassic 2.1W GU10 CW 36D ND UE SRT6

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDClassic 2.1W GU10 CW 36D ND UE SRT6

