



CorePro LED capsule MV

CorePro LEDcapsule 1.9–25W ND G9 827

CorePro, LEDspot, G9, 25 W, G9, 2700 K, 220 lm, CRI 80, 15000 hour(s), Plastic

This single-ended mains-voltage capsule for G9-base luminaires delivers directional light, making it a true alternative to halogen capsule lamps. It is particularly suitable for task lighting in shops, hotels and restaurants, and ideal for desk lamps and cabinet lighting. Compatible with existing fixtures with G9 holders and designed for retrofit replacement of halogen capsules, CorePro LEDcapsule delivers huge energy savings and minimizes maintenance costs, without any compromise on light quality.

Product data

General Information	
Cap-Base	G9
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot
Flux measurement reference	Sphere
Warranty period	2 years
Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	320 degree(s)
Luminous Flux	220 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	115 lm/W


Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG0
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	1.9 W
Lamp Current (Nom)	17 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220–240 V

CorePro LED capsule MV

Temperature	
T-Case Maximum (Nom)	92 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	G9
Net Weight (Piece)	0.006 kg
Approval and Application	
Energy Efficiency Class	E
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	2 kWh
EPREL Registration Number	1932582
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM) - Flickering value as per 1 EN 61000-3-3	

Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 to +45 °C
Application Conditions	
can it be used in closed luminaires	No
Product Data	
Order product name	CorePro LEDcapsule 1.9-25W ND G9 827
Full product name	CorePro LEDcapsule 1.9-25W ND G9 827
Full product code	872016930181800
Order code	929003790502
Material Nr. (12NC)	929003790502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169301818
Numerator - Packs per outer box	12
EAN/UPC - Case	8720169301825



Dimensional drawing



Product	D	C
CorePro LEDcapsule 1.9-25W ND G9 827	14 mm	43 mm


CorePro LED capsule MV

Photometric data




General uniform lighting - CorePro LEDcapsule 1.9-25W ND G9 827

Spectral Power Distribution Colour - CorePro LEDcapsule 1.9-25W ND G9 827



Light Distribution Diagram - CorePro LEDcapsule 1.9-25W ND G9 827

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - CorePro LEDcapsule 1.9-25W ND G9 827

CorePro LED capsule MV

