



MASTER Glass LED bulbs

MAS LEDBulbDT3.4 -40W E27 CRI95 A60 FR G

LEDbulb, A60, 40 W, E27, 2200 K, 2700 K, 470 lm, CRI 95, 25000 hour(s), Glass

LEDbulb, A60, 40 W, E27, 2200 K, 2700 K, 470 lm, CRI 95, 25000 hour(s), Glass, 138 lm/W, EEL D, PF 0.6, Beam angle 300 degree(s), RG1, IP20, SVM 0.4, PstLM 0.9

Product data

General Information	
Cap-Base	E27
Nominal lifetime	25,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LEDbulb
Flux measurement reference	Sphere
Warranty period	5 years
Light Technical	
Color Code	922-927 [CCT of 2200K-2700K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	470 lm
Color Designation	Warm Glow(WG)
Correlated Color Temperature (Nom)	2200 2700 K
Luminous Efficacy (rated) (Nom)	138 lm/W
Color Consistency	<6
Color rendering index (CRI)	95
LLMF At End Of Nominal Lifetime (Nom)	70 %

Photobiological safety according to EN 62471	RG1
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	3.4 W
Lamp Current (Nom)	24 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.6
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	Only with specific dimmers

MASTER Glass LED bulbs

Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Glass
Bulb Shape	A60
Net Weight (Piece)	0.031 kg

Approval and Application

Energy Efficiency Class	D
Energy Consumption kWh/1000 h	4 kWh
EPREL Registration Number	1969960
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	0.9
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 to +45 °C


Application Conditions

can it be used in closed luminaires	No
Wireless Technology	Not applicable

Product Data



Order product name	MAS LEDBulbDT3.4 -40W E27 CRI95 A60 FR G
Full product name	MAS LEDBulbDT3.4 -40W E27 CRI95 A60 FR G
Full product code	872016931103900
Order code	31103900
Material Nr. (12NC)	929003798902
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169311039
Numerator - Packs per outer box	10
EAN/UPC - Case	8720169311046

Dimensional drawing



Product	D	C
MAS LEDBulbDT3.4 -40W E27 CRI95 A60 FR G	60 mm	108 mm

Photometric data




Spectral Power Distribution Colour - MAS LEDBulbDT3.4 -40W E27 CRI95 A60 FR G

General uniform lighting - MAS LEDBulbDT3.4 -40W E27 CRI95 A60 FR G

MASTER Glass LED bulbs

Photometric data



Light Distribution Diagram - MAS LEDBulbDT3.4 -40W E27 CRI95 A60 FR G

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - MAS LEDBulbDT3.4 -40W E27 CRI95 A60 FR G

