Ref. Certif. No.

NL-126420

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Electronic Controlgear for LED modules
Name and address of the applicant	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the manufacturer	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the factory	
When more than one factory	☐ Additional information on page 2
Ratings and principal characteristics	**Product data** Ratings: Xitanium 40W/m 0.7-1.05A 44V DS I 230V Un: 220-240 Vac; In: 0,2 Aac; fn: 50/60 Hz; DC; PF: 0,9C; Un: 186-250 Vdc; In: 0,25-0,18 Adc; Pn: 45,9 W; Irated: 0,7-1,05 Adc; Prated: 40 W; Uout: 60 Vdc max; ta: -20…+45 · C; tc: +80 · C; SELV; EL; Independent Xitanium 30W/m 0.35-0.7A 44V DS I 230V Un: 220-240 Vac; In: 0,15 Aac; fn: 50/60 Hz; DC; PF: 0,9C; Un: 186-250 Vdc; In: 0,18-0,14 Adc; Pn: 34,6 W; Irated: 0,35-0,7 Adc; Prated: 30 W; Uout: 60 Vdc max; ta: -20…+45 · C; tc: +80 · C; SELV; EL; Independent Xitanium 20W/m 0.15-0.5A 44V DS I 230V Un: 220-240 Vac; In: 0,1 Aac; fn: 50/60 Hz; DC; PF: 0,9C; Un: 186-250 Vdc; In: 0,12-0,09 Adc; Pn: 21,8 W; Irated: 0,15-0,5 Adc; Prated: 20 W; Uout: 60 Vdc max; ta: -20…+45 · C; tc: +80 · C; SELV; EL; Independent Xitanium 40W/m 0.7-1.05A 44V DS S 230V Un: 220-240 Vac; In: 0,2 Aac; fn: 50/60 Hz; DC; PF: 0,9C; Un: 186-250 Vdc; In: 0,25-0,18 Adc; Pn: 45,4 W; Irated: 0,7-1,05 Adc; Prated: 40 W; Uout: 60 Vdc max; ta: -20…+50 · C; tc: +80 · C; SELV; EL; Built-in Xitanium 30W/m 0.35-0.7A 44V DS S 230V Un: 220-240 Vac; In: 0,15 Aac; fn: 50/60 Hz; DC; PF: 0,9C; Un: 186-250 Vdc; In: 0,19-0,14 Adc; Pn: 34 W; Irated: 0,35-0,7 Adc; Prated: 30 W; Uout: 60 Vdc max; ta: -20…+50 · C; tc: +80 · C; SELV; EL; Built-in

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-06-03

Signature: Miranda Zhou

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

	Xitanium 20W/m 0.15-0.5A 44V DS S 230V Un: 220-240 Vac; In: 0,1 Aac; fn: 50/60 Hz; DC; PF: 0,9C; Un: 186-250 Vdc; In: 0,12-0,09 Adc; Pn: 22,2 W; Irated: 0,15-0,5 Adc; Prated: 20 W; Uout: 60 Vdc max; ta: -20…+50 · C; tc: +80 · C; SELV; EL; Built-in
Trademark / Brand (if any)	PHILIPS, SIGNIFY, XITANIUM or ADVANCE
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	Xitanium 20W/m 0.15-0.5A 44V DS I 230V, Xitanium 20W/m 0.15-0.5A 44V DS S 230V, Xitanium 30W/m 0.35-0.7A 44V DS I 230V, Xitanium 30W/m 0.35-0.7A 44V DS S 230V, Xitanium 40W/m 0.7-1.05A 44V DS I 230V and Xitanium 40W/m 0.7-1.05A 44V DS S 230V
Additional information	☐ Additional information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61347-1:2015, IEC 61347-1:2015/AMD1:2017, IEC 61347-2-13:2014/AMD1:2016, IEC 61347-2-13:2014 and IEC 62384:2020 National differences: EU Group Differences
As shown in the Test Report Ref. No. which forms part of this Certificate	6271106.50 and 6271106.51

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-06-03

Signature: Miranda Zhou