

Certificate of Suitability

Global-Mark Pty. Ltd., certify the electrical equipment described hereunder complies with standards listed herein and notifies the certificate holder to affix the Regulatory Compliance Mark (RCM) mark on the product of the same type provided that the requirements of all relevant parts of AS/NZS 4417 applicable to the article are fulfilled. In placing the RCM mark on the product, the Responsible Supplier makes a declaration of compliance with the certification standard(s) and confirms that the product is identical to the product certified herein. This Certificate meets the requirements of a Recognised External Certification Scheme (RECS).

CERTIFICATION AND CERTIFICATE HOLDER DETAILS

Company Name	Signify Netherlands B.V	Other Name	
Address	High Tech Campus 48 Eindhoven - 5656 AE Netherlands		
Client ID	105985	Global-Mark File Number:	105985-114
Certification Number	GMA-520323	Revision Number	00
Certificate Standard(s)	AS 61347.2.13:2018 & AS/NZS 61347.1:2016 + A1 Lamp Control Gear - Part 2-13: Particular Requirements For D.C Or A.C Supplied Electronic Control Gear For Led Modules.		
Type of Certification	Electrical Safety Product	Scheme	Global-Mark Electrical Product Safety Certification Scheme

System 1 Approval

CERTIFICATE DATES

Certificate Issue Date	25/09/2024
Certificate Last Update Date	
Certification Expiry Date	25/09/2029

This certification remains valid until the above-mentioned expiry date and subject to the organisation's continued compliance with the certification standard, and Global-Mark's Terms and Conditions. This Certificate remains the property of Global-Mark Pty Ltd, Company Number: ACN.108-087-654. The use of the Accreditation Mark indicates accreditation by the Joint Accreditation System of Australia and New Zealand in respect to those activities covered by JAS-ANZ accreditation. Refer to www.jasanz.org/register for verification.



Certification Manager

Certificate of Suitability

CERTIFIED ELECTRICAL EQUIPMENT				
Declared Article	Product Description	Trade Name	Model Number	Rating
Non declared	Electronic Controlgear for LED modules	PHILIPS	Xitanium 150W 400-700mA 215V DS 230V	Uin: 220-240 Vac; Freq: 50/60 Hz; PF: 0,9C; Iin: 0,75 Aac; Pin: 156 W; Irated: 0,4 / 0,5 / 0,6 / 0,7 A; Prated: 150 W; Output voltage: 140-215 Vdc; Uout: 300 V; ta: -25...+50°C; tc: 85°C; built-in
Non declared	Electronic Controlgear for LED modules	PHILIPS	Xitanium 100W 350-500mA 200V DS 230V	Uin: 220-240 Vac; Freq: 50/60 Hz; PF: 0,9C; Iin: 0,5 Aac; Pin: 104 W; Irated: 0,35 / 0,4 / 0,45 / 0,5 A; Prated: 100 W; Output voltage: 100-200 Vdc; Uout: 250 V; ta: -25...+50°C; tc: 85°C; built-in
Non declared	Electronic Controlgear for LED modules	PHILIPS	Xitanium 80W 400-550mA 200V DS 230V	Uin: 220-240 Vac; Freq: 50/60 Hz; PF: 0,9C; Iin: 0,39 Aac; Pin: 84 W; Irated: 0,4 / 0,45 / 0,5 / 0,55 A; Prated: 80 W; Output voltage: 80-200 Vdc; Uout: 250 V; ta: -25...+50°C; tc: 85°C; built-in
Non declared	Electronic Controlgear for LED modules	PHILIPS	Xitanium 150W 400-700mA 215V DS 230V EL	Uin: 220-240 Vac or 186-250 Vdc; Freq: 50/60 Hz or DC; PF: 0,9C; Iin: 0,75 Aac or 0,6-0,85 Adc; Pin: 156 W; Irated: 0,4 / 0,5 / 0,6 / 0,7 A; Prated: 150 W; Output voltage: 140-215 Vdc; Uout: 300 V; ta: -25...+50°C; tc: 85°C; built-in
Non declared	Electronic Controlgear for LED modules	PHILIPS	Xitanium 100W 350-500mA 200V DS 230V EL	Uin: 220-240 Vac or 186-250 Vdc; Freq: 50/60 Hz or DC; PF: 0,9C; Iin: 0,5 Aac or 0,38-0,55 Adc; Pin: 104 W; Irated: 0,35 / 0,4 / 0,45 / 0,5 A; Prated: 100 W; Output voltage: 80-200 Vdc; Uout: 250 V; ta: -25...+50°C; tc: 85°C; built-in

This certification remains valid until the above-mentioned expiry date and subject to the organisation's continued compliance with the certification standard, and Global-Mark's Terms and Conditions. This Certificate remains the property of Global-Mark Pty Ltd, Company Number: ACN.108-087-654. The use of the Accreditation Mark indicates accreditation by the Joint Accreditation System of Australia and New Zealand in respect to those activities covered by JAS-ANZ accreditation. Refer to www.jasanz.org/register for verification.



Certification Manager

Page 2 of 3

Certificate of Suitability

Non declared	Electronic Controlgear for LED modules	PHILIPS	Xitanium 90W 200-350mA 256V DS 230V EL	U _{in} : 220-240 Vac or 186-250 Vdc; Freq: 50/60 Hz or DC; PF: 0,9C; I _{in} : 0,43 Aac or 0,34-0,49 Adc; Pin: 94 W; I _{rated} : 0,2 / 0,25 / 0,3 / 0,35 A; Prated: 90 W; Output voltage: 150-256 Vdc; U _{out} : 300 V; ta: -25...+50°C; tc: 85°C; built-in
--------------	--	---------	---	--

RELEVANT TRADEMARK (S)

COMMENTS OR CONDITIONS ON THE CERTIFICATION
Nil

End of document

This certification remains valid until the above-mentioned expiry date and subject to the organisation's continued compliance with the certification standard, and Global-Mark's Terms and Conditions. This Certificate remains the property of Global-Mark Pty Ltd, Company Number: ACN.108-087-654. The use of the Accreditation Mark indicates accreditation by the Joint Accreditation System of Australia and New Zealand in respect to those activities covered by JAS-ANZ accreditation. Refer to www.jasanz.org/register for verification.



Certification Manager



Page 3 of 3