Ref. Certif. No.

NL-126389

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Electronic Controlgear for LED modules
Name and address of the applicant	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the manufacturer	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the factory	
When more than one factory	☐ Additional information on page 2
Ratings and principal characteristics	**Product data** Ratings: Xitanium 42W 0.7-1.05A 40V HE 3CW 230V Xitanium 42W 0.7-1.05A 40V HE 3CB 230V Xitanium 42W 0.7-1.05A 40V HE 3CG 230V Un: 220-240 Vac; fn: 50/60 Hz; PF: 0,9C; In: 0,14/0,15/0,16/0,17/0,18/0,19/0,20/0,21 Aac; Pn: 30/32/34/36/39/41/43/45 W; Irated: 0,70/0,75/0,80/0,85/0,90/0,95/1,00/1,05 Adc; Prated: 28/30/32/34/36/38/40/42 W; Uoutput: 25-40 Vdc, Uout: 60 Vdc max; ta: -20…+35 °C; tc: 80 °C; Built-in; SELV Xitanium 28W 0.35-0.7A 40V HE 3CW 230V Xitanium 28W 0.35-0.7A 40V HE 3CB 230V Xitanium 28W 0.35-0.7A 40V HE 3CG 230V Un: 220-240 Vac; fn: 50/60 Hz; PF: 0,85C/0,9C; In: 0,07/0,08/0,09/0,10/0,11/0,12/0,13/0,14 Aac; Pn: 16/18/20/22/24/26/28/30 W; Irated: 0,35/0,40/0,45/0,50/0,55/0,60/0,65/0,70 Adc; Prated: 14/16/18/20/22/24/26/28 W; Uoutput: 30-40 Vdc, Uout: 60 Vdc max; ta: -20…+35 °C; tc: 80 °C; Built-in; SELV Xitanium 12W 0.15-0.3A 40V HE 3CW 230V Xitanium 12W 0.15-0.3A 40V HE 3CB 230V Xitanium 12W 0.15-0.3A 40V HE 3CG 230V Un: 220-240 Vac; fn: 50/60 Hz; PF: 0,85C/0,9C; In: 0,04/0,05/0,06/0,07 Aac; Pn: 7/9/12/14 W; Irated: 0,15/0,20/0,25/0,30 Adc; Prated: 6/8/10/12 W; Uoutput: 30-40 Vdc, Uout: 60 Vdc max; ta: -20…+35 °C; tc: 80 °C; Built-in; SELV
Trademark / Brand (if any)	PHILIPS, SIGNIFY, XITANIUM or ADVANCE

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-06-03

Signature: Miranda Zhou

Ref. Certif. No.

NL-126389

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	Xitanium 12W 0.15-0.3A 40V HE 3CB 230V, Xitanium 12W 0.15-0.3A 40V HE 3CG 230V, Xitanium 12W 0.15-0.3A 40V HE 3CW 230V, Xitanium 28W 0.35-0.7A 40V HE 3CB 230V, Xitanium 28W 0.35-0.7A 40V HE 3CG 230V, Xitanium 28W 0.35-0.7A 40V HE 3CW 230V, Xitanium 42W 0.7-1.05A 40V HE 3CB 230V, Xitanium 42W 0.7-1.05A 40V HE 3CG 230V and Xitanium 42W 0.7-1.05A 40V HE 3CW 230V
Additional information	☐ Additional information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61347-1:2015, IEC 61347-1:2015/AMD1:2017, IEC 61347-2-13:2014, IEC 61347-2-13:2014/AMD1:2016 and IEC 62384:2020 National differences: EU Group Differences
As shown in the Test Report Ref. No. which forms part of this Certificate	6271240.50 and 6271240.51

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-06-03

Signature: Miranda Zhou