


ENEC License

License

ENEC-05164-A2

Issue date

2025-04-30



This is to acknowledge that

SIGNIFY NETHERLANDS B.V.

HIGH TECH CAMPUS 48 EINDHOVEN 5656 AE NETHERLANDS

has had

Built-in LED Controlgear

**LED Power Driver 100u 24V 120V-277V, LED Power Driver 80W
24V 120V-277V**

evaluated and meets the requirements of the standard

**EN 61347-2-13:2014, EN 61347-2-13:2014/A1:2017, EN
61347-1:2015, EN 61347-1:2015/A1:2021, EN IEC
62384:2020**

Test Report Nos. 4791629945.1 Amendment 3 issued on 2025-04-28
4791629945.2 Amendment 4 issued on 2025-04-28

Certification Manager
Thomas Wilson

**UL International Demko A/S, Borupvang 5A, 2750 Ballerup, Denmark,
Tel. +45 44 85 65 65**

See UL Product iQ® at <https://iq.ulprospector.com> for additional information.

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this License, in accordance with the ENEC Requirements. The Designated License holder is entitled to use the ENEC 15 Mark (as shown in annex 1) for the Certified Product manufactured at the production site(s) identified above in accordance with the ENEC Mark Service Agreement including without limitation the ENEC Mark Testing and Certification Services Service Terms. Only those Products bearing the ENEC Mark should be considered as being covered by UL's ENEC Mark Service. This License shall remain valid unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this License is amended or withdrawn prior the Date of Withdrawal of conflicting Standard(s).




ENEC LICENSE

TECHNICAL DETAILS

Production site(s)

Trademark PHILIPS

Ratings LED Power Driver 100u 24V 120V-277V:
Input: 120-277 V~ 50/60 Hz 0.91-0.4 A λ :0.95
Output: 24 V $\overline{=}$ 4 A $\overline{=}$ 96 W max.;
tc= +90°C;

LED Power Driver 80W 24V 120V-277V:
Input: 120-277 V~ 50/60 Hz 0.76-0.36 A λ :0.95
Output: 24 V $\overline{=}$ 3.33 A $\overline{=}$ 80 W max.;
tc= +85°C.
ta= -30...+60°C, Class II   SELV 

Additional Information

The report was revised to include administrative modifications.
This certificate replaces previous certificate no. ENEC-05164-M2
issued on 2025-04-23, due to
- Update photo

Additional information:

- The above mentioned control gears fulfil the relevant
requirements according to:

IEC/EN 60335-2-24, IEC/EN 60335-2-89

The control gear has been also evaluated according to Annex CC
of IEC/EN 60335-2-24 and Annex BB of IEC/EN 60335-2-29.

Models (continued from page 1)

ENEC LICENSE FORM OF THE ENEC MARK



15 is the identification number of the Certification Body

Size of the mark:

The size of the mark may be reduced on the condition that it remains legible and that the ratio $b/a=1,7$ is kept.