Ref. Certif. No.

NL-126345

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Electronic controlgear for LED modules
Name and address of the applicant	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the manufacturer	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the factory	
When more than one factory	☒ Additional information on page 3
Ratings and principal characteristics	**Product data** Ratings: Xi CR 75W 0.2-1.05A SDMP 230V C123 sXt Uin: 220-240 V; fn: 50/60 Hz; Iin: 0,39-0,36 A; Pin: 84 W; PF: 0,9C; Uoutput: 35-150 Vdc, Uout = 200 V max; Irated: 200-1050 mA; Prated: 75 W; ta: -40…+55 °C; tc: 85 °C; Built-in Xi CR 40W 0.2-1.05A SDMP 230V C123 sXt Uin: 220-240 V; fn: 50/60 Hz; Iin: 0,22-0,20 A; Pin: 47 W; PF: 0,9C; Uoutput: 20-77 Vdc, Uout = 100 V max; Irated: 200-1050 mA; Prated: 40 W; ta: -40…+55 °C; tc: 85 °C; SELV; Built-in Xi CR 22W 0.2-1.05A SDMP 230V C123 sXt Uin: 220-240 V; fn: 50/60 Hz; Iin: 0,13-0,12 A; Pin: 28 W; PF: 0,9C; Uoutput: 8-48 Vdc, Uout = 80 V max; Irated: 200-1050 mA; Prated: 22 W; ta: -40…+60 °C; tc: 80 °C; SELV; Built-in Xi CR 75W .2-1.05A SDMP 230 C123 TR sXt Uin: 220-240 V; fn: 50/60 Hz; Iin: 0,39-0,36 A; Pin: 84 W; PF: 0,9C-0,98; Uoutput: 35-150 Vdc, Uout = 200 V max; Irated: 200-1050 mA; Prated: 75 W; ta: -40…+55 °C; tc: 85 °C; Built-in Xi CR 40W .2-1.05A SDMP 230 C123 TR sXt Uin: 220-240 V; fn: 50/60 Hz; Iin: 0,22-0,20 A; Pin: 47 W; PF: 0,9C-0,98; Uoutput: 20-77 Vdc, Uout = 100 V max; Irated: 200-1050 mA; Prated: 40 W; ta: -40…+55 °C; tc: 85 °C; SELV; Built-in Xi CR 22W .2-1.05A SDMP 230 C123 TR sXt

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-06-02

Signature: Carol Jwo

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

	Uin: 220-240 V; fn: 50/60 Hz; Iin: 0,13-0,12 A; Pin: 28 W; PF: 0,9C-0,98; Uoutput: 8-48 Vdc, Uout = 80 V max; Irated: 200-1050 mA; Prated: 22 W; ta: -40…+60 °C; tc: 80 °C; SELV; Built-in
Trademark / Brand (if any)	XITANIUM, ADVANCE, PHILIPS or SIGNIFY
Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	Xi CR 22W .2-1.05A SDMP 230 C123 TR sXt, Xi CR 22W 0.2-1.05A SDMP 230V C123 sXt, Xi CR 40W .2-1.05A SDMP 230 C123 TR sXt, Xi CR 40W 0.2-1.05A SDMP 230V C123 sXt, Xi CR 75W .2-1.05A SDMP 230 C123 TR sXt and Xi CR 75W 0.2-1.05A SDMP 230V C123 sXt
Additional information	☐ Additional information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61347-1:2015, IEC 61347-1:2015/AMD1:2017, IEC 61347-2-13:2014, IEC 61347-2-13:2014/AMD1:2016 and IEC 62384:2020 National differences: EU Group Differences
As shown in the Test Report Ref. No. which forms part of this Certificate	6271227.50 and 6271227.51

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-06-02

Signature: Carol Jwo

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

Additional factory

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-06-02

Signature: Carol Jwo