# Australia and New Zealand Certificate of Suitability- addendum

**Certificate**
ULL-103699-A2

**Issue date**
2026-06-05

**Expiration date**
2029-12-17

This is to acknowledge that

## Signify Netherlands B.V.

High Tech Campus 48, EINDHOVEN 5656 AE
Netherlands

has had

## Electronic Control gear for LED modules {component for building in}

[refer following page(s) for models list]

evaluated and meets the requirements of the standard(s)

## AS 61347.2.13:2018; AS/NZS 61347.1:2016, Amd 1: 2018, Amd 2: 2025

ANZ Certification Scheme requirements.

Amarjit Singh (Certification Officer)

Certification Body:
UL International New Zealand Limited,
54 Tarndale Grove, Albany, Auckland 0632, New Zealand.

Issued for use in Australia and New Zealand only.
All dates are in Year-Month-Day format (YYYY-MM-DD).

JAS-ANZ

www.jasanz.org/register

UL Solutions



© 2026 UL LLC. All rights reserved.

# Australia and New Zealand
# Certificate of Suitability-addendum

**Certificate No:** ULL-103699-A2
**Original Date of Certification:** 2024-12-17
**Date of Issue/Revision:** 2026-06-05

**Trade Name or Trademark:** PHILIPS, SIGNIFY, XITANIUM, ADVANCE

**Risk Class / NSW Declared Class:** EESS OUT OF SCOPE - Non-prescribed / non-declared

**IEC Standard Country Differences:** AU and NZ

**Certification Marking:** The RCM may be applied to the product and all the requirements of all relevant parts of AS/NZS 4417 applicable to the article shall be fulfilled.

**Additional Certification Conditions:** None.

**Model Details and Ratings:**

Model: Xi CR 22W 0.2-1.05A SDMP 230V C123 sXt
Ratings: Uin: 220-240 V, fn: 50/60 Hz, Iin: 0.13-0.12 A, Pin: 28 W, PF: 0.9C,
Uoutput: 8-48 Vdc, Uout = 80 V max,
Irated: 200-1050 mA, Prated: 22 W, ta: -40…+60 °C, tc: 80 °C,
SELV, Built-in

Model: Xi CR 40W 0.2-1.05A SDMP 230V C123 sXt
Ratings: Uin: 220-240 V, fn: 50/60 Hz, Iin: 0.22-0.20 A, Pin: 47 W, PF: 0.9C,
Uoutput: 20-77 Vdc, Uout = 100 V max,
Irated: 200-1050 mA, Prated: 40 W, ta: -40…+55 °C, tc: 85 °C,
SELV, Built-in

Model: Xi CR 75W 0.2-1.05A SDMP 230V C123 sXt
Ratings: Uin: 220-240 V, fn: 50/60 Hz, Iin: 0.39-0.36 A, Pin: 84 W, PF: 0.9C,
Uoutput: 35-150 Vdc, Uout = 200 V max,
Irated: 200-1050 mA, Prated: 75 W, ta: -40…+55 °C, tc: 85 °C,
Built-in

Details of addendum :
- Add trade names “XITANIUM”, and “ADVANCE”.


© 2026 UL LLC. All rights reserved.