Ref. Certif. No.

NL-126895

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Electronic controlgear for LED modules
Name and address of the applicant	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the manufacturer	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the factory	
When more than one factory	☐ Additional information on page 2
Ratings and principal characteristics	**Product data** Ratings: Xitanium 75W 0.25-0.5A 230V DALI DS 230V Uin:220-240 Vac; Iin: 0,37 Aac; fn: 50/60 Hz; DC; PF: 0,92C-0,98; Uin:186-250 Vdc; Iin: 0,20-0,26 Adc; Pin: 81 W; Uoutput: 115-230 Vdc, Uout: 250 Vdc max.; Irated: 0,25-0,5 Adc; Prated: 75 W; ta: -25…+50 °C; tc: 80 °C; Built-in; Output not mains isolated Xitanium 60W 0.12-0.35A 220V DALI DS230V Uin:220-240 Vac; Iin: 0,3 Aac; fn: 50/60 Hz; DC; PF: 0,92C-0,98; Uin:186-250 Vdc; Iin: 0,17-0,22 Adc; Pin: 66 W; Uoutput: 110-220 Vdc, Uout: 250 Vdc max.; Irated: 0,12-0,35 Adc; Prated: 60 W; ta: -25…+50 °C; tc: 80 °C; Built-in; Output not mains isolated Xitanium 40W 0.1-0.35A 120V DALI DS 230V Uin:220-240 Vac; Iin: 0,2 Aac; fn: 50/60 Hz; DC; PF: 0,92C-0,98; Uin:186-250 Vdc; Iin: 0,11-0,14 Adc; Pin: 44 W; Uoutput: 60-120 Vdc, Uout: 250 Vdc max.; Irated: 0,1-0,35 Adc; Prated: 40 W; ta: -25…+50 °C; tc: 80 °C; Built-in; Output not mains isolated Xitanium 20W 0.1-0.35A 60V DALI DS 230V Uin:220-240 Vac; Iin: 0,1 Aac; fn: 50/60 Hz; DC; PF: 0,89C-0,98; Uin:186-250 Vdc; Iin: 0,07-0,09 Adc; Pin: 23 W; Uoutput: 30-60 Vdc, Uout: 250 Vdc max.; Irated: 0,1-0,35 Adc; Prated: 20 W; ta: -25…+50 °C; tc: 80 °C; Built-in; Output not mains isolated
Trademark / Brand (if any)	PHILIPS, SIGNIFY, XITANIUM or ADVANCE

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-06-17

Signature: May Liu

Ref. Certif. No.

NL-126895

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	Xitanium 20W 0.1-0.35A 60V DALI DS 230V, Xitanium 40W 0.1-0.35A 120V DALI DS 230V, Xitanium 60W 0.12-0.35A 220V DALI DS230V and Xitanium 75W 0.25-0.5A 230V DALI DS 230V
Additional information	☐ Additional information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61347-1:2015, IEC 61347-1:2015/AMD1:2017, IEC 61347-2-13:2014, IEC 61347-2-13:2014/AMD1:2016 and IEC 62384:2020 National differences: EU Group Differences
As shown in the Test Report Ref. No. which forms part of this Certificate	6271345.50 and 6271345.51

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-06-17

Signature: May Liu