Australia and New Zealand Certificate of Suitability

Certificate
ULL-104174

Issue date
2025-10-15

Expiration date
2030-10-15

This is to acknowledge that

Signify Netherlands B.V.

High Tech Campus 48, EINDHOVEN 5656 AE
Netherlands

has had

Electronic controlgear for LED modules

[refer following page(s) for models list]

evaluated and meets the requirements of the standard(s)

AS/NZS 61347.1:2016, Amd 1: 2018, Amd 2: 2025; AS 61347.2.13:2018

ANZ Certification Scheme requirements.

Stuart Foster (Certification Officer)

Certification Body:
UL International New Zealand Limited,
54 Tarndale Grove, Albany, Auckland 0632, New Zealand.

Issued for use in Australia and New Zealand only.
All dates are in Year-Month-Day format (YYYY-MM-DD).

JAS-ANZ

www.jasanz.org/register

UL Solutions

© 2025 UL LLC. All rights reserved.

Australia and New Zealand
Certificate of Suitability

Certificate No: ULL-104174
Date of Issue/Revision: 2025-10-15

Trade Name or Trademark: PHILIPS, SIGNIFY

Risk Class / NSW Declared Class: EESS OUT OF SCOPE - Non-prescribed / non-declared

IEC Standard Country Differences: AU and NZ

Certification Marking: The RCM may be applied to the product and all the requirements of all relevant parts of AS/NZS 4417 applicable to the article shall be fulfilled.

Additional Certification Conditions: Product is a component for building in.

Model Details:

Model Name
Xitanium 75W 0.25-0.5A 230V DALI DS 230V
Xitanium 60W 0.12-0.35A 220V DALI DS230V
Xitanium 40W 0.1-0.35A 120V DALI DS 230V
Xitanium 20W 0.1-0.35A 60V DALI DS 230V

Additional Information:

Xitanium 75W 0.25-0.5A 230V DALI DS 230V
Uin:220-240 Vac, Iin: 0.37 Aac, fn: 50/60 Hz, DC, PF: 0.92C-0.98,
Uin:186-250 Vdc, Iin: 0.20-0.26 Adc, Pin: 81 W,
Uoutput: 115-230 Vdc, Uout = 250 Vdc max.,
Irated: 0.25-0.5 Adc, Prated: 75 W, ta: -25…+50 °C, tc(max): 80 °C,
Built-in, Output not mains isolated

Xitanium 60W 0.12-0.35A 220V DALI DS230V
Uin:220-240 Vac, Iin: 0.3 Aac, fn: 50/60 Hz, DC, PF: 0.92C-0.98,
Uin:186-250 Vdc, Iin: 0.17-0.22 Adc, Pin: 66 W,
Uoutput: 110-220 Vdc, Uout = 250 Vdc max.,
Irated: 0.12-0.35 Adc, Prated: 60 W, ta: -25…+50 °C, tc(max): 80 °C,
Built-in, Output not mains isolated

Xitanium 40W 0.1-0.35A 120V DALI DS 230V
Uin:220-240 Vac, Iin: 0.2 Aac, fn: 50/60 Hz, DC, PF: 0.92C-0.98,
Uin:186-250 Vdc, Iin: 0.11-0.14 Adc, Pin: 44 W,
Uoutput: 60-120 Vdc, Uout = 250 Vdc max.,
Irated: 0.1-0.35 Adc, Prated: 40 W, ta: -25…+50 °C, tc(max): 80 °C,
Built-in, Output not mains isolated

Xitanium 20W 0.1-0.35A 60V DALI DS 230V
Uin:220-240 Vac, Iin: 0.1 Aac, fn: 50/60 Hz, DC, PF: 0.89C-0.98,
Uin:186-250 Vdc, Iin: 0.07-0.09 Adc, Pin: 23 W,
Uoutput: 30-60 Vdc, Uout = 250 Vdc max.,
Irated: 0.1-0.35 Adc, Prated: 20 W, ta: -25…+50 °C, tc(max): 80 °C,
Built-in, Output not mains isolated

© 2025 UL LLC. All rights reserved.