Xitanium

Datasheet

Xitanium non-Isolated DALI Dip Switch

Xitanium 40W 0.1-0.35A 120V DALI DS 230V
9290 040 06806

Xitanium LED non-isolated DALI Dipswitch drivers are ideal for high-voltage (HV) systems. They are based on three pillars: quality of light, reliability, and flexibility. Our drivers' robustness is based on in-depth electronics knowledge and extensive testing. Finally, application-oriented operating windows offer the flexibility required to provide the stable lumen output and quality levels that lighting specifiers and architects demand.

Benefits

- High quality of light
- Peace of mind with proven reliability
- Selectable and programmable output current enables flexibility and SKU reduction

Features

- High efficiency
- Low Ripple less than 4%
- 4 selectable output currents by programmable Dip switches
- 50,000 hours lifetime @ Tc-max

Application

- Offices
- Waterproof
- Retail: supermarkets, shopping malls

Logistical data

Specification item	Value
Product name	Xitanium 40W 0.1-0.35A 120V DALI DS 230V
EOC	872790097663200
Logistic code 12NC	9290 040 06806
EAN1 (GTIN)	8727900976632
EAN3 (box)	8727900976649
Pieces per box	20

Electrical input data

Specification item	Value	Unit	Condition
Rated input voltage range	220...240	V_{ac}	Performance range
Rated input voltage	230	V_{ac}	
Rated input frequency	50...60	Hz	Performance range
Rated input current	0.19	A	@ rated output power @ rated input voltage
Rated input power	44.0	W	@ rated output power @ rated input voltage
Power factor	0.98		@maximum output power @ rated input voltage
Total harmonic distortion	20	%	@ rated output power @ rated input voltage
Efficiency	≥ 90.0	%	@ maximum output power @ rated input voltage @ max. Uoutput
Rated input voltage DC	186...250	V_{dc}	Performance range; EOFi = 95%
Rated input current DC	0.11...0.14	A_{dc}	Performance range
Input voltage AC	198...264	V_{ac}	Operational range
Input frequency AC	47.5...63	Hz	Operational range
Input voltage DC	168...275	V_{dc}	Operational range
Standby Power (W)	0.5	W	
Isolation input to output	No		

Electrical output data

Specification item	Value	Unit	Condition
Regulation method	Constant Current		
Output voltage	60...120	V_{dc}	
Output voltage max.	250	V	Maximum output voltage (rms)
Output current	100...350	mA	Via dipswitches:
Min output current	10	mA	
Output current tolerance ±	5	%	@full load
Output current ripple LF	≤ 5	%	Ripple = peak / average, < 3kHz, ≤ 6% @ DC input
Output current ripple HF	≤ 15	%	
Output P_{st}^{LM}	≤ 1.0		In entire voltage range for each choice of output current
Output SVM	≤ 0.4		In entire voltage range for each choice of output current
Output power	12.0...40.0	W	Performance range: 12...40W
Number of output channels	1		

Control interfaces

Specification item	Value	Unit	Condition
Control method	DALI		Output current can be set via dip switches
Dimming range	5...100	%	Default range

Wiring and Connections

Specification item	Value	Unit	Type
Input wire cross-section	0.5...1.5 / 20...16	mm^2 / AWG	WAGO744, solid wire
Input wire strip length	8...9	mm	
Output wire cross-section	0.5...1.5 / 20...16	mm^2 / AWG	WAGO744, solid wire
Output wire strip length	8...9	mm	
Maximum cable length	2	m	CISPR15: between driver and LED module

Isolation

Insulation per IEC61347-1	Input	Output	DALI
Input	-	No	Basic
Output	No	-	Basic
DALI	Basic	Basic	-

Dimensions and weight

Specification item	Value	Unit	Tolerance (mm)
Length (A1)	210	mm	± 0.3
Mounting hole distance (A2)	198.5	mm	± 0.3
Width (B1)	30	mm	± 0.5
Height (C1)	21	mm	± 0.5
Mounting hole diameter (D1)	4.1	mm	± 0.2
Mounting hole diameter (D2)	4.1	mm	± 0.2
Weight	150	gram	
Housing color	White		



Operational temperatures and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-25...+50	°C	Higher ambient temperature allowed as long as Tcase-max is not exceeded
Tcase-max	80	°C	Maximum temperature measured at T_{case}-point
Tcase-life	70	°C	Measured at T_{case}-point
Maximum housing temperature	110	°C	In case of a failure, inherent by design
Relative humidity	10...90	%	Non-condensing

Lifetime

Specification item	Value	Unit	Condition
Driver lifetime	100,000	hours	Measured temperature at Tcase-point is Tcmax - 10 degrees. Maximum failures = 10%
Driver lifetime Tcmax	50,000	hours	Measured temperature at Tcase-point is Tc-max. Maximum failures = 10%



Maximum failures = 10%

Maximum failures = 10%

Storage temperature and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-25...+85	°C	
Relative humidity	5...95	%	Non-condensing

Programmable features

Specification item	Available	Default setting	Condition
Set Adjustable Output Current (AOC)	DipSwitch	200 mA	Set the output current via the dipswitch, see wiring diagram for an overview
Adjustable Light Output (ALO)	Yes	OFF	
Constant Light Output (CLO)	Yes	OFF	
Min Dim Level (%)	Yes	5 %	
DC emergency (DCemDim)	Yes	ON	%100
OEM Write Protection (OWP)	Yes	OFF	
Luminaire Info (DALI part 251)	Yes		
Luminaire maintenance (DALI part 253)	Yes		

Non-programmable features

Specification item	Value	Condition
Open load protection	Yes	Automatic recovering
Short circuit protection	Yes	Automatic recovering
Over power protection	Yes	Automatic recovering
Hot wiring	No	
Suitable for fixtures with protection class	I	per IEC60598
Output Overvoltage Detection	Yes	
Energy metering (DALI part 252)	Yes	
Diagnostics (DALI part 253)	Yes	

Inrush current

Specification item	Value	Unit	Condition
Inrush current	20	A	Input voltage 230V
Inrush peak width	209	µs	Input voltage 230V, measured at 50% height
Drivers / MCB 16A type B @230V AC	≤ 32	pcs	Input voltage 230V



Please refer to the driver design in guide if you use other MCB-types.

If several mini circuit breakers are used directly side-by-side (without distance pieces a correction factor of 80% has to be applied to the rated current

Driver touch current / protective conductor current / earth leakage current

Specification item	Value	Unit	Condition
Typical Protective Conductor Current (ins. Class I)	0.5	mA rms	Acc. IEC60598-1. LED module contribution not included

Surge immunity

Specification item	Value	Unit	Condition
Mains surge immunity (diff. mode)	1	kV	L- N Acc. IEC61000-4-5. 2 Ohm, 1.2/50us, 8/20us
Mains surge immunity (comm. mode)	2	kV	L/N - PE Acc. IEC61000-4-5. 12 Ohm, 1.2/50us, 8/20us
Control surge immunity (diff. mode)	0.8	kV	DALI/TD - DALI-TD Acc. IEC61000-4-5. 2 Ohm, 1.2/50us, 8/20us
Control surge immunity (comm. mode)	2	kV	DALI/TD - PE, DALI - L/N Acc. IEC61000-4-5. 12 Ohm, 1.2/50us, 8/20us

Application Info (Approbation)

Specification item	Value
Approval marks and Certifications	BIS / CB / CCC / CE / DALI 2 / EAC / EL / ENEC / RCM / UA / UKCA
Ingress Protection classification (IP)	20
Application	Indoor Linear
Mounting Type	Built-in

Graphs

Operating window



Type	Output current (mA)	Min. output voltage (V)	Max. output voltage (V)	Max. output power (W)
Xitanium 40W 0.1-0.35A 120V DALI DS 230V	100	120	120	12
Xitanium 40W 0.1-0.35A 120V DALI DS 230V	150	80	120	18
Xitanium 40W 0.1-0.35A 120V DALI DS 230V	200	60	120	24
Xitanium 40W 0.1-0.35A 120V DALI DS 230V	250	60	120	30
Xitanium 40W 0.1-0.35A 120V DALI DS 230V	300	60	120	36
Xitanium 40W 0.1-0.35A 120V DALI DS 230V	350	60	114	40

Power factor versus output power



Efficiency versus output power



THD versus output power



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.