



Deep Recessed Spotlight

RS350 G2 RC Rd D75 11W 35K 15D 1H

Deep Recessed Spotlight, 11 W, 1000 lm, 3500 K, High-gloss mirror, Dark gray

Deep Recessed offers excellent experience for the consumer, which includes eye comfort, reliable quality and outstanding performance, especially the anti glare feature.

Product data

General Information		Photobiological safety according to EN 62471	
Light source replaceable	No		RG1
Number of gear units	1 unit		
Driver included	Yes		
Nominal lifetime	25,000 hour(s)		
Switching Cycle	15,000		
Warranty period	1 years		
Light Technical		Operating and Electrical	
Luminous Flux	1,000 lm	Input Voltage	220 to 240 V
Correlated Color Temperature (Nom)	3500 K	Input Frequency	50 or 60 Hz
Luminous Efficacy (rated) (Nom)	90 lm/W	Inrush current	8.5 A
Color rendering index (CRI)	90	Inrush time	0.18 ms
Number of light sources	1	Power Consumption	11 W
Light source color	935 warm white	Warm-up time to 60% light	<2 s
Optic type	High-gloss mirror	Power Factor (Fraction)	0.5
Luminaire light beam spread	15°	Connection	Flying leads/wires
		Cable	Cable 0.1m without plug
		Number of products on MCB of 16 A type B	110
		Suitable for random switching	Not applicable
		Protection class IEC	Safety class II

Deep Recessed Spotlight

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die-cast
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Dark gray
Optical cover finish	Clear
Overall height	80 mm
Overall diameter	84 mm
Net weight	0.25 kg
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Net Weight (Piece)	0.250 kg

Approval and Application

Insulation Coverage Rating	Non IC Rating
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
EU RoHS compliant	Yes

Warranty	3 year(s)
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.4033, 0.3800) <5SDCM
Power consumption tolerance	+/-10%


Over Time Performance (IEC Compliant)

Median useful life L70B50	25,000 hour(s)
---------------------------	----------------

Product Data



Order product name	RS350 G2 RC Rd D75 11W 35K 15D 1H
Full product name	RS350 G2 RC Rd D75 11W 35K 15D 1H
Full product code	694197061289000
Order code	929004098910
Material Nr. (12NC)	929004098910
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6941970612890
Numerator - Packs per outer box	12
EAN/UPC - Case	6941970612906

Dimensional drawing



Deep Recessed Spotlight

Photometric data



General uniform lighting - RS350 G2 RC Rd D75 11W 35K 15D 1H

Light Distribution Diagram - RS350 G2 RC Rd D75 11W 35K 15D 1H

