



MASTER LED tube EM/Mains T8 with Recycled Plastic

MAS LEDtube 1500mm HO 16.7W 840 T8 EELB

MASTER, LEDtube, T8, EM/Mains, 1500 mm, 16.7 W, 58W TL-D, 4000 K, 3100 lm, CRI 80, 75000 hour(s)

MASTER, LEDtube, T8, EM/Mains, 1500 mm, 16.7 W, LED alternative to 58W TL-D, 4000 K, 3100 lm, CRI 80, 75000 hour(s), 185 lm/W, EEL B, G13 Rotatable end-cap, Beam angle 160 degree(s), Plastic, 40 %, 1500 mm, RGO, SDCM 6, PF 0.9, IP20, SVM 0.1, PstLM 0.1

Product data

General Information		Operating and Electrical	
Cap-Base	G13 Rotatable end-cap	Luminous Efficacy (rated) (Nom)	185 lm/W
Nominal lifetime	75,000 hour(s)	Color Consistency	<6
Switching Cycle	200,000	Color rendering index (CRI)	80
Lighting Technology	LEDtube	LLMF At End Of Nominal Lifetime (Nom)	70 %
Flux measurement reference	Sphere	Photobiological safety according to EN 62471	RGO
Warranty period	5 years		
Light Technical		Input Frequency	50 to 60 Hz
Color Code	840 [CCT of 4000K]	Power Consumption	16.7 W
Beam Angle (Nom)	160 degree(s)	Lamp Current (Max)	84 mA
Luminous Flux	3,100 lm	Lamp Current (Min)	70 mA
Color Designation	Cool White (CW)	Starting Time (Nom)	0.5 s
Correlated Color Temperature (Nom)	4000 K	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.9

MASTER LED tube EM/Mains T8 with Recycled Plastic

Voltage (Nom)	220-240 V
LED alternative to fluorescent lamp power	58W TL-D
Inrush current at mains	7.7
Max. lamp no. on MCB B type 10A – Mains	90
Max. lamp no. on MCB B type 10A – EM ballast without Compensation Capacitor.	90
Max. lamp no. on MCB B type 10A – EM ballast with Compensation Capacitor.	10
Max. lamp no. on MCB B type 16A – Mains	150
Max. lamp no. on MCB B type 16A – EM ballast without Compensation Capacitor.	150
Max. lamp no. on MCB B type 16A – EM ballast with Compensation Capacitor.	16
Ballast Compatibility	EM/Mains

Temperature

T-Case Maximum (Nom)	50 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Plastic
Product Length	1,500 mm
Bulb Shape	T8
Net Weight (Piece)	0.265 kg

Approval and Application

Energy Efficiency Class	B
Energy Saving Product	Yes
Approval Marks	RoHS compliance CE marking KEMA Keur certificate ENEC certificate

Energy Consumption kWh/1000 h	17 kWh
EPREL Registration Number	2571894
CE mark	Yes
EU RoHS compliant	Yes
LED Innovations	UltraEfficient
Flickering value (PstLM) – Flickering value as per EN 61000-3-3	0.1
Stroboscopic effect visibility measure (SVM)	0.1
Ambient temperature range	-20 to +45 °C
Post-consumer recycled plastic material ratio	40 %

Application Conditions

can it be used in closed luminaires	Yes
Wireless Technology	Not applicable


Sustainability Data

Sustainability rating	Signify Circle
Product non-virgin material ratio	25.8 %

Product Data

Order product name	MAS LEDtube 1500mm HO 16.7W 840 T8 EELB
Full product name	MAS LEDtube 1500mm HO 16.7W 840 T8 EELB
Full product code	872016938813000
Order code	929004242802
Material Nr. (12NC)	929004242802
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169388130
Numerator - Packs per outer box	10
EAN/UPC - Case	8720169388147


Dimensional drawing




Product	D1	D2	A1	A2	A3
MAS LEDtube 1500mm HO 16.7W 840 T8 EELB	25.8 mm	28 mm	1,498.8 mm	1,505.9 mm	1,513 mm

MASTER LED tube EM/Mains T8 with Recycled Plastic


Photometric data



Spectral Power Distribution Colour - MAS LEDtube 1500mm HO 16.7W 840 T8 EELB




Light Distribution Diagram - MAS LEDtube 1500mm HO 16.7W 840 T8 EELB




General Uniform Lighting
Copyright © 2015 Philips Lighting B.V. Page 1/1

General uniform lighting - MAS LEDtube 1500mm HO 16.7W 840 T8 EELB

Lifetime



Lumen Maintenance Diagram - MAS LEDtube 1500mm HO 16.7W 840 T8 EELB



Life Expectancy Diagram

MASTER LED tube EM/Mains T8 with Recycled Plastic

Lifetime



Lumen Maintenance Diagram - MAS LEDtube 1500mm HO 16.7W 840 T8 EELB

Life Expectancy Diagram



Life Expectancy Diagram

