



MASTER VALUE LED spot MV

MAS LEDspotVLE D 3.7-50W GU10 930 36D UK

MASTER Value, LEDspot, PAR16, 50 W, GU10, 3000 K, 365 lm, CRI 90, 25000 hour(s), Glass

Delivering a warm, halogen-like accent beam, MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it realizes more natural colors, creating cozy and comfortable ambiances for residential and hospitality projects, and emphasizing the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. MASTER VALUE also offers more energy savings than normal LED spots.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information	
Cap-Base	GU10
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot
Flux measurement reference	Narrow Cone

Warranty period	5 years
Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	36 degree(s)
Luminous Flux	365 lm
Luminous Intensity (Nom)	750 cd

MASTER VALUE LED spot MV

Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	98 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	365 lm
Photobiological safety according to EN 62471	RG1

Operating and Electrical

Input Frequency	50 to 60 Hz
Power Consumption	3.7 W
Lamp Current (Nom)	27 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.6
Voltage (Nom)	220-240 V

Temperature

T-Case Maximum (Nom)	66 °C
----------------------	-------

Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------

Mechanical and Housing

Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	PAR16
Net Weight (Piece)	0.041 kg

Approval and Application

Energy Efficiency Class	E
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	4 kWh
EPREL Registration Number	2150469
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 to +45 °C


Application Conditions

can it be used in closed luminaires	No
-------------------------------------	----

Product Data

Order product name	MAS LEDspotVLE D 3.7-50W GU10 930 36D UK
Full product name	MAS LEDspotVLE D 3.7-50W GU10 930 36D UK
Full product code	872016939922800
Order code	929004248098
Material Nr. (12NC)	929004248098
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169399228
Numerator - Packs per outer box	10
EAN/UPC - Case	8720169399235



Dimensional drawing



Product	D	C
MAS LEDspotVLE D 3.7-50W GU10 930 36D UK	50 mm	54 mm

MASTER VALUE LED spot MV


Photometric data



© 2016 Philips Lighting B.V. Page 17


Spectral Power Distribution Colour - MAS LEDspotVLE D 3.7-50W GU10 930 36D UK

Accent Lighting Spots - MAS LEDspotVLE D 3.7-50W GU10 930 36D UK




Light Distribution Diagram - MAS LEDspotVLE D 3.7-50W GU10 930 36D UK

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - MAS LEDspotVLE D 3.7-50W GU10 930 36D UK

MASTER VALUE LED spot MV

