


PHILIPS

Xitanium

LED driver



Datasheet

Xitanium UHE drivers

Xitanium UHE 26W 0.5-0.65A 40V DS I 230V

9290 048 31601

Single current LED drivers for essential lighting applications.

Xitanium LED UHE drivers are designed to fulfill the market needs for high efficiency and reliable performance. Xitanium drivers have common features such as low ripple output current, adjustable output current by dip switch and 100,000 hours lifetime. They are specifically designed to ensure great EMI performance, high robustness and safe usage.

Features

- Efficiency up to 93.5%
- 100,000 hours lifetime @Tc-life
- 4 output currents by dip switch
- SELV output for simpler approval process and easy design-in
- Low ripple output current

Benefits

- Various lout choice for high volume application
- Comfort for eyes and assurance of camera-friendly performance
- Easy to manage stock with dip switch
- Independent-version housing design for stand-alone installations

Application

- Public buildings (airports, cinemas, theaters, exhibition halls)
- Retail (supermarkets, shops)
- Office

Logistical data

Specification item	Value
Product name	Xitanium UHE 26W 0.5-0.65A 40V DS I 230V
Logistic code 12NC	9290 048 31601
Pieces per box	64
Weight	89 gram

Electrical input data

Specification item	Value	Unit	Condition
Rated input voltage range	220...240	V _{ac}	Performance range
Rated input voltage	230	V _{ac}	
Rated input frequency	50...60	Hz	Performance range
Rated input current	0.14	A	@ rated output power @ rated input voltage
Rated input power	29.0	W	@ rated output power @ rated input voltage
Power factor	0.96		@maximum output power @ rated input voltage
Total harmonic distortion	20	%	@ rated output power @ rated input voltage
Efficiency	93.5	%	@ maximum output power @ rated input voltage
Input voltage AC	198...264	V _{ac}	Operational range
Input frequency AC	45...66	Hz	Operational range
Isolation input to output	Reinforced		

Electrical output data


Specification item	Value	Unit	Condition
Regulation method	Constant Current		
Output voltage	30...40	V _{dc}	
Output voltage max.	60	V	Maximum output voltage (rms)
Output current	500 / 550 / 600 / 650	mA	
Output current tolerance ±	8	%	@full load
Output current ripple LF	≤ 1	%	Ripple = peak to average < 3kHz
Output current ripple HF	≤ 15	%	Ripple = peak to average total
Output P _{st} ^{LM}	≤ 0.1		In entire operating window
Output SVM	≤ 0.1		In entire operating window
Output power	15.0...26.0	W	
Rated output power	26.0	W	

Control interfaces

Specification item	Value	Unit	Condition
Control method	Fixed		

Wiring and Connections

Specification item	Value	Unit	Type
Input wire cross-section	0.75...1.5 / 18...16	mm ² / AWG	Type250, solid / stranded wire. Applicable cable outer jacket diameter: 3mm to 8mm
Input wire strip length	8.5...9.5	mm	
Output wire cross-section	0.2...1.5 / 24...16	mm ² / AWG	Type250, solid / stranded wire. Applicable cable outer jacket diameter: 3mm to 8mm
Output wire strip length	8.5...9.5	mm	
Maximum cable length	0.6	m	Total length of wiring including LED module, one way




Isolation

Insulation per IEC61347-1	Input	Output	Housing
Input	-	Reinforced	Reinforced
Output	Reinforced	-	Basic
Housing	Reinforced	Basic	-

Dimensions and weight

Specification item	Value	Unit	Tolerance (mm)
Length (A1)	125.8	mm	
Mounting hole distance (A2)	115.8	mm	
Width (B1)	43	mm	
Width (B2)	25.3	mm	
Height (C1)	25	mm	
Mounting hole diameter (D1)	3.9	mm	
Mounting hole diameter (D2)	3.9	mm	
Weight	89	gram	
Housing color	white		




Operational temperatures and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-20...+50	°C	
Tcase-max	75	°C	Lifetime 50khrs@Tc max.
Tcase-life	65	°C	Lifetime 100khrs@Tc max -10°C measured at T _c -point
Maximum housing temperature	110	°C	In case of a failure, inherent by design
Relative humidity	10...90	%	Non-condensing

Lifetime

Specification item	Value	Unit	Condition
Driver lifetime	50,000	hours	Measured temperature at Tcase-point is Tcase-max. Maximum failures = 10%
Driver lifetime	100,000	hours	Measured temperature at Tcase-point is Tcase-max -10 degrees. Maximum failures = 10%



Maximum failures = 10%

Storage temperature and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-25...+85	°C	
Relative humidity	5...95	%	Non-condensing

Non-programmable features


Specification item	Value		Condition
Open load protection	Yes		Automatic recovering
Short circuit protection	Yes		Automatic recovering
Over power protection	Yes		Automatic recovering
Hot wiring	No		
Suitable for fixtures with protection class	II		per IEC60598

Inrush current

Specification item	Value	Unit	Condition
Inrush current	33.43	A	Input voltage 230V
Inrush peak width	116	μs	Input voltage 230V, measured at 50% height
Drivers / MCB 16A type B @230V AC	≤ 34	pcs	Input voltage 230V

Please refer to the driver design in guide if you use other MCB-types.

If several mini circuit breakers are used directly side-by-side (without distance pieces)
a correction factor of 80% has to be applied to the rated current



Driver touch current / protective conductor current / earth leakage current


Specification item	Value	Unit	Condition
Typical Touch Current (ins. Class II)	0.7	mA peak	Acc. IEC61347-1. LED module contribution not included

Surge immunity


Specification item	Value	Unit	Condition
Mains surge immunity (diff. mode)	1	kV	Acc. IEC61000-4-5. 2 Ohm, 1.2/50us, 8/20us
Mains surge immunity (comm. mode)	2	kV	Acc. IEC61000-4-5. 12 Ohm, 1.2/50us, 8/20us

Application Info (Approbation)


Specification item	Value
Approval marks and Certifications	CB / CCC / CE / ENEC / RCM / SELV / TISI / UKCA
Ingress Protection classification (IP)	20
Noise and hum dB(A)	20
Application	Indoor
Mounting Type	Independent




Power factor versus output power



Efficiency versus output power



THD versus output power



Notes

Electrical Specifications:

- 1) All the specifications are typical and at 25°C Ta unless specified otherwise.
- 2) Efficiency will not below 93.0% @ max rated output power.



©2025 Signify Holding, IBRS 10461, 5600 VB, NL. All rights reserved.
UK importer address: Signify Commercial UK Limited, 2 Guildford Business Park, GU2 8XG, UK.

The information provided herein is subject to change without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

Date of release: August 28, 2025 v1

www.philips.com/oem