

PHILIPS

CertaFlux

LED

CertaFlux RDL vertical
center G1



Datasheet

CertaFlux RDL LED system

Key features and benefits

- Lowest Total Cost of Ownership with rapid payback times
- Efficacy up to 120 lm/W for vertical center lighting
- Choice of color temperatures 2700 K, 3000 K, 4000 K, Meat Color
- Natural merchandise color with specially formulated CRI >80 LEDs
- Led engine lengths optimized to standard lengths optimized for the application
- Plug and play system for easy and fast assembly
- Miniaturized slim design for aesthetic integration
- Built-in lens provides bright illumination for attractive merchandising
- Enhanced safety with 24 V supply (Safety Extra Low Voltage – SELV)
- Virtually maintenance-free due to long life-time: >50,000 hours
- True System proposition with Philips Constant Voltage LED power drivers and accessories
- Five year system warranty

October 2021



Ordering data

Commercial product name	EOC	12NC	Box quantity
CertaFlux RDL vrt 1500mm 827 CTR WGS G1	8719514 421103 00	9290 034 07606	24
CertaFlux RDL vrt 1500mm 830 CTR WGS G1	8718699 621247 00	9290 016 66506	24
CertaFlux RDL vrt 1500mm 840 CTR WGS G1	8718699 621261 00	9290 016 66606	24
CertaFlux RDL vrt 1500mm MC CTR WGS G1	8718699 621285 00	9290 016 66706	24
CertaFlux RDL vrt 1650mm 830 CTR WGS G1	8718699 621360 00	9290 016 67106	24
CertaFlux RDL vrt 1650mm 840 CTR WGS G1	8718699 621384 00	9290 016 67206	24
CertaFlux RDL vrt 1650mm MC CTR WGS G1	8718699 621407 00	9290 016 67306	24

Module temperatures

Parameter	Nominal*	Life**	Max***	Unit
T _a (ambient temperature)	5	30	30	°C

* Nominal value at which typical performance is specified

** Value at which life time is specified

*** Maximum value for safe operation, do not operate above this value

Optical characteristics - table per color (CCT)


CertaFlux RDL vrt 1500mm 827 CTR WGS G1

Parameter	Min	Typ	Max	Unit
Luminous flux	2178	2420	2904	lm
Correlated color temperature (CCT)		2700		K
Color coordinates (CIEx, CIEy)		(0.458, 0.41)		-
Color consistency			5	SDCM
CRI	80			
Photobiological safety			RG1 unlimited	

Measurement precision flux +/- 5%, for efficacy +/- 6%., for x, y +/- 0.005, for CRI +/- 1.5

This product contains a light source of energy efficiency class E.
EPREL model identifier: L71000000410-27.
Registration number: 896648.

This product contains a light source of energy efficiency class E.
EPREL model identifier: L71000000410-27.
Registration number: 896649.




CertaFlux RDL vrt 1500mm 830 CTR WGS G1

Parameter	Min	Typ	Max	Unit
Luminous flux	2178	2420	2904	lm
Correlated color temperature (CCT)		3000		K
Color coordinates (CIEx, CIEy)		(0.435, 0.407)		-
Color consistency			5	SDCM
CRI	80			
Photobiological safety			RG1 unlimited	

Measurement precision flux +/- 5%, for efficacy +/- 6%., for x, y +/- 0.005, for CRI +/- 1.5

This product contains a light source of energy efficiency class E.
EPREL model identifier: L71000000410-30.
Registration number: 896650.

This product contains a light source of energy efficiency class E.
EPREL model identifier: L71000000420-30.
Registration number: 896651.




CertaFlux RDL vrt 150mm 840 CTR WGS G1

Parameter	Min	Typ	Max	Unit
Luminous flux	2178	2420	2904	lm
Correlated color temperature (CCT)		4000		K
Color coordinates (CIEx, CIEy)		(0.382, 0.382)		-
Color consistency			5	SDCM
CRI	80			
Photobiological safety			RG1 unlimited	

Measurement precision flux +/- 5%, for efficacy +/- 6%., for x, y +/- 0.005, for CRI +/- 1.5

This product contains a light source of energy efficiency class E.
EPREL model identifier: L71000000410-40.
Registration number: 896652.


This product contains a light source of energy efficiency class E.
EPREL model identifier: L71000000420-40.
Registration number: 896653.



CertaFlux RDL vrt 1500mm MC CTR WGS G1

Parameter	Min	Typ	Max	Unit
Luminous flux	2034	2260	2712	lm
Color coordinates (CIEx, CIEy)		(0.391, 0.334)		-
Color consistency			5	SDCM
CRI	80			
Photobiological safety			RG1 unlimited	

Measurement precision flux +/- 5%, for efficacy +/- 6%., for x, y +/- 0.005, for CRI +/- 1.5




CertaFlux RDL vrt 1650mm 830 CTR WGS G1

Parameter	Min	Typ	Max	Unit
Luminous flux	2376	2640	3168	lm
Correlated color temperature (CCT)		3000		K
Color coordinates (CIEx, CIEy)		(0.435, 0.407)		-
Color consistency			5	SDCM
CRI	80			
Photobiological safety			RG1 unlimited	

Measurement precision flux +/- 5%, for efficacy +/- 6%., for x, y +/- 0.005, for CRI +/- 1.5

This product contains a light source of energy efficiency class E.
EPREL model identifier: L71000000430-30.
Registration number: 896657.




This product contains a light source of energy efficiency class E.
EPREL model identifier: L71000000440-30.
Registration number: 896658.

CertaFlux RDL vrt 1650mm 840 CTR WGS G1

Parameter	Min	Typ	Max	Unit
Luminous flux	2376	2640	3168	lm
Correlated color temperature (CCT)		4000		K
Color coordinates (CIEx, CIEy)		(0.382, 0.382)		-
Color consistency			5	SDCM
CRI	80			
Photobiological safety			RG1 unlimited	

Measurement precision for flux +/- 5%, for efficacy +/- 6%., for x, y +/- 0.005, for CRI +/- 1.5

This product contains a light source of energy efficiency class E.
EPREL model identifier: L71000000430-40.
Registration number: 896604.





This product contains a light source of energy efficiency class E.
EPREL model identifier: L71000000440-40.
Registration number: 896605.

CertaFlux RDL vrt 1650mm MC CTR WGS G1

Parameter	Min	Typ	Max	Unit
Luminous flux	2232	2480	2976	lm
Color coordinates (CIEx, CIEy)		(0.391, 0.334)		-
Color consistency			5	SDCM
CRI	80			
Photobiological safety			RG1 unlimited	

Measurement precision for flux +/- 5%, for efficacy +/- 6%., for x, y +/- 0.005, for CRI +/- 1.5





Electrical characteristics

CertaFlux RDL vrt 1500mm 827 CTR WGS G1

CertaFlux RDL vrt 1500mm 830 CTR WGS G1

CertaFlux RDL vrt 1500mm 840 CTR WGS G1

Parameter	Min	Typ	Max	Unit
Forward voltage		24.0		V
Power consumption		19.8		W = kWh/1000h

CertaFlux RDL vrt 1500mm MC CTR WGS G1

Parameter	Min	Typ	Max	Unit
Forward voltage		24.0		V
Power consumption		26.5		W = kWh/1000h

CertaFlux RDL vrt 1650mm 830 CTR WGS G1

CertaFlux RDL vrt 1650mm 840 CTR WGS G1

Parameter	Min	Typ	Max	Unit
Forward voltage		24.0		V
Power consumption		21.6		W = kWh/1000h

CertaFlux RDL vrt 1650mm MC CTR WGS G1

Parameter	Min	Typ	Max	Unit
Forward voltage		24.0		V
Power consumption		28.9		W = kWh/1000h

Lumen maintenance

Operation point	Lumen maintenance x 1000 hours	L70			L80		
		B50	B20	B10	B50	B20	B10
	Ta -20°C	>54	>54	>54	>54	>54	>54
	Ta 5°C	>54	>54	>54	>54	>54	>54
	Ta 30°C	>54	>54	>54	49	47	47

Mechanical characteristics (all sizes are guaranteed at Ta:25 °C)


CertaFlux RDL vrt 1500mm 827 CTR WGS G1

CertaFlux RDL vrt 1500mm 830 CTR WGS G1

CertaFlux RDL vrt 1500mm 840 CTR WGS G1

CertaFlux RDL vrt 1500mm MC CTR WGS G1

Parameter	Min	Typ	Max	Unit
Length	1498	1500	1502	mm
Width	24.7	25	25.3	mm
Height	24.5	25	25.5	mm
Product mass		284		gram




CertaFlux RDL vrt 1650mm 830 CTR WGS G1

CertaFlux RDL vrt 1650mm 840 CTR WGS G1

CertaFlux RDL vrt 1650mm MC CTR WGS G1

Parameter	Min	Typ	Max	Unit
Length	1648	1650	1652	mm
Width	24.7	25	25.3	mm
Height	24.5	25	25.5	mm
Product mass		314		gram



Absolute ratings

Parameter	Min	Max	Unit
Case temperature (T _c -max)		70	°C
ESD (direct contact)		4	kV
ESD (air)		8	kV
Working voltage		60	V _{dc}
Ambient temperature	-30	30	°C
Storage temperature	-30	60	°C

Application information

Certificates and Standards

CE/CB/ENEC

UKCA

UL

NSF

CQC

DLC

IEC/EN 62031

UL 2108

GB 24819

Relevant clauses of IEC/EN 60335-1

Annex CC of IEC/EN 60335-2-24

Annex BB of IEC/EN 60335-2-89

Environmental

RoHS/REACH

Application

IP rating	IP54, IK02
Overheating protection	No protection
Luminaire class	IEC Class III when connected to a SELV Philips Constant Voltage 24 VDC drivers
Dimming	Yes

Notes

Modules with MC color are out of scope of ecodesign requirement due to special color point.



© 2021 Signify Holding, IBRS 10461, 5600VB, NL. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

www.philips.com/oem

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.
UK importer address: 3, Guildford Business Park, GU2 8XG

01/09/2021