


PHILIPS

CertaFlux

LED

CertaFlux RDL vertical
side G1



Datasheet

CertaFlux RDL LED system

Key features and benefits

- Lowest Total Cost of Ownership with rapid payback times
- Efficacy up to 120 lm/W for vertical side lighting
- Choice of color temperatures 3000 K, 4000 K, Meat Color
- Natural merchandise color with specially formulated CRI >80 LEDs
- Led engine lengths optimized to standard lengths optimized for the application
- Plug and play system for easy and fast assembly
- Miniaturized slim design for aesthetic integration
- Built-in lens provides bright illumination for attractive merchandising
- Enhanced safety with 24 V supply (Safety Extra Low Voltage – SELV)
- Virtually maintenance-free due to long life-time: >50,000 hours
- True System proposition with Philips Constant Voltage LED power drivers and accessories
- Five year system warranty

September 2021



indirect



instant

Ordering data

Commercial product name	EOC	12NC	Box quantity
CertaFlux RDL vrt 1500mm 830 SD WGS G1	8718699 621186 00	9290 016 66206	24
CertaFlux RDL vrt 1500mm 840 SD WGS G1	8718699 621209 00	9290 016 66306	24
CertaFlux RDL vrt 1500mm MC SD WGS G1	8718699 621223 00	9290 016 66406	24
CertaFlux RDL vrt 1650mm 830 SD WGS G1	8718699 621308 00	9290 016 66806	24
CertaFlux RDL vrt 1650mm 840 SD WGS G1	8718699 621322 00	9290 016 66906	24
CertaFlux RDL vrt 1650mm MC SD WGS G1	8718699 621346 00	9290 016 67006	24

Module temperatures

Parameter	Nominal*	Life**	Max***	Unit
T _a (ambient temperature)	5	30	30	°C

* Nominal value at which typical performance is specified

** Value at which life time is specified


*** Maximum value for safe operation, do not operate above this value

Optical characteristics - table per color (CCT)

CertaFlux RDL vrt 1500mm 830 SD WGS G1

Parameter	Min	Typ	Max	Unit
Luminous flux	1040	1155	1386	lm
Correlated color temperature (CCT)		3000		K
Color coordinates (CIEx, CIEy)		(0.435, 0.407)		-
Color consistency			5	SDCM
CRI		80		
Photobiological safety			RG1 unlimited	


Measurement precision for flux +/- 5%, for efficacy +/- 6%., for x, y +/- 0.005, for CRI +/- 1.5



CertaFlux RDL vrt 1500mm 840 SD WGS G1

Parameter	Min	Typ	Max	Unit
Luminous flux	1040	1155	1386	lm
Correlated color temperature (CCT)		4000		K
Color coordinates (CIEx, CIEy)		(0.382, 0.382)		-
Color consistency			5	SDCM
CRI		80		
Photobiological safety			RG1 unlimited	


Measurement precision for flux +/- 5%, for efficacy +/- 6%., for x, y +/- 0.005, for CRI +/- 1.5



CertaFlux RDL vrt 1500mm MC SD WGS G1

Parameter	Min	Typ	Max	Unit
Luminous flux	981	1090	1308	lm
Color coordinates (CIEx, CIEy)		(0.391, 0.334)		-
Color consistency			5	SDCM
CRI	80			
Photobiological safety			RG1 unlimited	

Measurement precision for flux +/- 5%, for efficacy +/- 6%., for x, y +/- 0.005, for CRI +/- 1.5




CertaFlux RDL vrt 1650mm 830 SD WGS G1

Parameter	Min	Typ	Max	Unit
Luminous flux	1143	1270	1524	lm
Correlated color temperature (CCT)		3000		K
Color coordinates (CIEx, CIEy)		(0.435, 0.407)		-
Color consistency			5	SDCM
CRI	80			
Photobiological safety			RG1 unlimited	




Measurement precision for flux +/- 5%, for efficacy +/- 6%., for x, y +/- 0.005, for CRI +/- 1.5



CertaFlux RDL vrt 1650mm 840 SD WGS G1

Parameter	Min	Typ	Max	Unit
Luminous flux	1143	1270	1524	lm
Correlated color temperature (CCT)		4000		K
Color coordinates (CIEx, CIEy)		(0.382, 0.382)		-
Color consistency			5	SDCM
CRI	 80			
Photobiological safety			RG1 unlimited	


Measurement precision for flux +/- 5%, for efficacy +/- 6%., for x, y +/- 0.005, for CRI +/- 1.5




CertaFlux RDL vrt 1650mm MC SD WGS G1

Parameter	Min	Typ	Max	Unit
Luminous flux	1080	1200	1440	lm
Color coordinates (CIEx, CIEy)		(0.391, 0.334)		-
Color consistency			5	SDCM
CRI	80			
Photobiological safety			RG1 unlimited	

Measurement precision for flux +/- 5%, for efficacy +/- 6%., for x, y +/- 0.005, for CRI +/- 1.5





Electrical characteristics

CertaFlux RDL vrt 1500mm 830 SD WGS G1

CertaFlux RDL vrt 1500mm 840 SD WGS G1

Parameter	Min	Typ	Max	Unit
Forward voltage		24.0		V
Power consumption		9.40		W = kWh/1000h

CertaFlux RDL vrt 1500mm MC SD WGS G1

Parameter	Min	Typ	Max	Unit
Forward voltage		24.0		V
Power consumption		12.8		W = kWh/1000h

CertaFlux RDL vrt 1650mm 830 SD WGS G1

CertaFlux RDL vrt 1650mm 840 SD WGS G1

Parameter	Min	Typ	Max	Unit
Forward voltage		24.0		V
Power consumption		10.8		W = kWh/1000h

CertaFlux RDL vrt 1650mm MC SD WGS G1

Parameter	Min	Typ	Max	Unit
Forward voltage		24.0		V
Power consumption		14.2		W = kWh/1000h


Lumen maintenance

Operation point	Lumen maintenance x 1000 hours	L70			L80		
		B50	B20	B10	B50	B20	B10
	Ta -20°C	>54	>54	>54	>54	>54	>54
	Ta 5°C	>54	>54	>54	>54	>54	>54
	Ta 30°C	>54	>54	>54	51	50	50

Mechanical characteristics


CertaFlux RDL vrt 1500mm 830 SD WGS G1
 CertaFlux RDL vrt 1500mm 840 SD WGS G1
 CertaFlux RDL vrt 1500mm MC SD WGS G1

Parameter	Min	Typ	Max	Unit
Length	1498.8	1500	1501.2	mm
Width	22.9	23.2	23.5	mm
Height	24.2	24.7	25.2	mm
Product mass		264		gram



CertaFlux RDL vrt 1650mm 830 SD WGS G1
 CertaFlux RDL vrt 1650mm 840 SD WGS G1
 CertaFlux RDL vrt 1650mm MC SD WGS G1

Parameter	Min	Typ	Max	Unit
Length	1498.8	1650	1501.2	mm
Width	22.9	23.2	23.5	mm
Height	24.2	24.7	25.2	mm
Product mass		292		gram



Absolute ratings

Parameter	Min	Max	Unit
Case temperature (Tc-max)		70	°C
ESD (direct contact)	4		kV
ESD (air)	8		kV
Ambient temperature	-30	30	°C
Storage temperature	-30	60	°C

Application information

Certificates and Standards

IEC/EN 62031

IEC/EN 62471

Relevant clauses of IEC/EN 60335-1

Annex CC of IEC/EN 60335-2-24

Annex BB of IEC/EN 60335-2-89

ENEC

UL 2108

CSA C22.2 No.9.0-96

CSA C22.2 No.250.0-08

NSF

CQC

DLC

Environmental

RoHS/REACH

Application

IP rating	IP54, IK02
Overheating protection	No protection
Luminaire class	IEC Class III when connected to a SELV Philips Constant Voltage 24 VDC drivers
Dimming	Yes

Notes

Special colors; Modules with MC color are special purpose modules for refrigerated cabinets, not for general lighting.



© 2021 Signify Holding, IBRS 10461, 5600VB, NL. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

www.philips.com/oem

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.
UK importer address: 3 Guildford Business Park, GU2 8XG

13/09/2021