



Ref. Certif. No.

**DK-76491-P2-A2-UL**

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

**CB TEST CERTIFICATE**

Product

Constant Voltage LED Module

Name and address of the applicant

Signify Netherlands B.V.  
High Tech Campus 48 Eindhoven 5656 AE  
THE Netherlands

Name and address of the manufacturer

Signify Netherlands B.V.  
High Tech Campus 48 Eindhoven 5656 AE  
THE Netherlands

Name and address of the factory

Note: When more than one factory, please report on page 2

☐ Additional Information on page 2

Ratings and principal characteristics

24 V  $\text{---}$  Pmax: 28,9 W tc: 70 °C (see test report for further ratings)

Trademark (if any)



Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

CertaFlux RDL a xmm zcc f Gg s

☒ Additional Information on page 2

Additional information (if necessary may also be reported on page 2)

The report was revised to include administrative modifications.

☒ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62031:2018

As shown in the Test Report Ref. No. which forms part of this Certificate

4789986639.2-1 issued on 2022-04-13

This CB Test Certificate is issued by the National Certification Body



- ☐ UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☒ UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2022-04-15

Original Issue Date: 2021-09-14

Signature:

Jan-Erik Storgaard



Ref. Certif. No.

**DK-76491-P2-A2-UL**

**Additional Model Detail(s):**

CertaFlux RDL a xmm zcc f Gg s

Where:

- a = Application Indication (may be "shelf" or "canopy" or "vrt" (vertical))
- x = Module length in mm (three or four digits, maximum value 1650)
- z = CRI of LED divided by 10 (one digit, may be "7" or "8" or "9" or blank)
- cc = CCT of LED divided by 100 (two characters, may be a value of maximum 40 or "MC")
- f = Fixture Type (may be "SD WGS" or "CTR WGS" or blank)
- g = Number of LED module's generation (may be "1")
- s = Commercial suffix for commercial purposes (optional)

**Additionally evaluated to:** EN IEC 62031:2020, IEC TR 62778:2014

National Differences specified in the CB Test Report.

**Summary of Modifications:**

- Change factory address

**Additional information (if necessary)**




- ☐ UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☒ UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2022-04-15

Original Issue Date: 2021-09-14

Signature:

  
Jan-Erik Storgaard