

CERTIFICATE

Issued to:
Applicant:
Signify (China) Investment Co., Ltd.
Building No.9, Lane 888, Tianlin Road, Minhang
District
200233 Shanghai, China

Licensee:
Signify Netherlands B.V.
High Tech Campus 48
5656 AE Eindhoven, Netherlands

Product : LED tube
Trade name(s) : PHILIPS
Type(s)/model(s) : 9290043069, 9290043070, 9290043071, 9290043072, 9290043073,
9290043074, 9290043075, 9290043076 and 9290043077

The product and any acceptable variation thereof as specified in the Annex to this certificate and the documents referred to therein.

DEKRA hereby declares that the above-mentioned product has been certified based on:

- a type test according to EN 62776:2015
- an inspection of the factory location according to CENELEC Operational Document CIG 021
- a DEKRA certification agreement with the number 6069605


DEKRA hereby grants the right to use the DEKRA Mark.

The DEKRA Mark may be applied to the product as specified in this certificate for the duration and under the conditions of the DEKRA Mark certification agreement.

This certificate is issued on 16 December 2025 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 31-168681

DEKRA Certification B.V.



B.T.M. Holtus
Managing Director



Kreny Lin
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL



31-168681

DEKRA Mark is the new KEMA-KEUR

The DEKRA Mark certificate for this product is to all intents and purposes equivalent to a KEMA-KEUR certificate, the other certification mark used by DEKRA and should be valued and used as such. DEKRA Mark is gradually replacing KEMA-KEUR.

For more information please check: [Introducing DEKRA Mark](#)

SPECIFICATION OF THE CERTIFIED PRODUCT**Product data**

Product	: LED tube
Trade name(s)	: PHILIPS
Type(s)/model(s)	: 9290043069, 9290043070, 9290043071, 9290043072, 9290043073, 9290043074, 9290043075, 9290043076 and 9290043077
Rated voltage	: 220-240 Vac or 186-250 Vdc
Nature of supply	: ac or dc
Rated frequency	: 50/60 Hz or 0 Hz (dc)
Degree of protection	: To be used in dry location
Futher information	: Rewiring type; 4000 K

Product data – type 9290043069

Rated input power	: 10,5 W
Supply Current	: 39 mA - 56 mA
Length	: 550 mm
Colour temperature (CCT)	: 3000 K

Product data – type 9290043070

Rated input power	: 10,5 W
Supply Current	: 39 mA - 56 mA
Length	: 550 mm
Colour temperature (CCT)	: 4000 K

Product data – type 9290043071

Rated input power	: 10,5 W
Supply Current	: 39 mA - 56 mA
Length	: 550 mm
Colour temperature (CCT)	: 6500 K

Product data – type 9290043072

Rated input power	: 26 W
Supply Current	: 100 mA -145 mA
Length	: 1150 mm
Colour temperature (CCT)	: 3000 K

Product data – type 9290043073

Rated input power	: 26 W
Supply Current	: 100 mA -145 mA
Length	: 1150 mm
Colour temperature (CCT)	: 4000 K

Product data – type 9290043074

Rated input power	: 26 W
-------------------	--------

Supply Current : 100 mA -145 mA
Length : 1150 mm
Colour temperature (CCT) : 6500 K

Product data – type 9290043075

Rated input power : 26 W
Supply Current : 100 mA -145 mA
Length : 1450 mm
Colour temperature (CCT) : 3000 K

Product data – type 9290043076

Rated input power : 26 W
Supply Current : 100 mA -145 mA
Length : 1450 mm
Colour temperature (CCT) : 4000 K

Product data – type 9290043077

Rated input power : 26 W
Supply Current : 100 mA -145 mA
Length : 1450 mm
Colour temperature (CCT) : 6500 K

TESTS**Test requirements**

EN 62776:2015

Test result

The test results are documented in DEKRA test file 6237663.50.

Additional information

The lamp complies with applicable clauses of EN 61347-2-13: 2014+A1:2017 (Lamp controlgear- particular requirements for d.c. or a.c. supplied electronic controlgear for LED modules) as the following:

- J.6 Emergency supply current
- J.7 EMC immunity
- J.8 Pulse voltage from central battery systems
- J.10 Temperature cycling test and endurance test

The lamp complies with applicable clauses of EN IEC 60598-2-22:2022 (Luminaires- particular requirements- Luminaires for emergency lighting) as the following:

- 22.17.3 Luminous flux measurement
- 22.19 High temperature operation

The product also complies with EN 62493:2015+A1:2022 in certificate

The list of components is laid down in test report 6237663.50.

Conclusion

The examination has confirmed that all requirements were met.

Factory location

