
Philips Lighting

Installation Instruction

LED WELL GLASS

Industrial Luminaire




Type : BY300P Lamp : 36 LED Voltage : 240 V, 50 Hz IP Classification : IP 65


Net Weight : 1.2 kgs
Max. Projected Area : 0.038 m²


IP-65


ta 45°














Caution

- Ensure Earthing is connected.
 Ensure 3 core CABLE for Connections (diameter 6-7mm)
- 3. Cable Entry gland should be properly tightened.
- 4. Product should be operated between 160-270V a.c.
- 5. Use Surge protection (upto 10kV) to protect against surges Use type B+C surge type SPD in distribution box to arrest switching and lighting surges.

FAILURE OF PRODUCT DUE TO NON COMPLIANCE TO ANY OF THE ABOVE. **VOIDS WARRANTY OF PRODUCT**