

# ENEC LICENSE

License No. ENEC-02242-P2-A2

Page 1/3

Date of Issue 2022-06-09

**License Holder** SIGNIFY NETHERLANDS B.V.  
HIGH TECH CAMPUS 48 EINDHOVEN 5656 AE  
THE NETHERLANDS

**Production site**

**Certification Mark** See Annex 1  
**Certified Product** Constant Voltage LED Module

**Model** CertaFlux RDL a xmm zcc f Gg s  
See page 2 for additional Information

**Trademark**

**PHILIPS** or  or **ADVANCE**

**Ratings** 24 V === Pmax: 28,9 W tc: 70 °C (see test report for further ratings)  
**Tested acc. to** EN IEC 62031:2020  
**Test Report No.** 4789986639.2-1 issued on 2022-04-13  
**Additional Information** The report was revised to include administrative modifications.  
See page 2 for additional information

---

**Certification Manager**  
Jan-Erik Storgaard

**Certification Body**

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this License, in accordance with the ENEC Requirements. The Designated License holder is entitled to use the ENEC 15 Mark (as shown in annex 1) for the Certified Product manufactured at the production site(s) identified above in accordance with the ENEC Mark Service Agreement including without limitation the ENEC Mark Testing and Certification Services Service Terms. Only those Products bearing the ENEC Mark should be considered as being covered by UL's ENEC Mark Service. This License shall remain valid unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this License is amended or withdrawn prior the Date of Withdrawal of conflicting Standard(s).

UL International Demko A/S, Borupvang 5A, DK-2750  
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com  
www.ul.com



# ENEC LICENSE

License No. ENEC-02242-P2-A2  
Page 2/3  
Date of Issue 2022-06-09

## Additional Model(s):

**Series:** CertaFlux RDL a xmm zcc f Gg s

Product Key:

Where:

- a = Application Indication (may be "shelf" or "canopy" or "vrt" (vertical));
- x = Module length in mm (three or four digits, maximum value 1650);
- z = CRI of LED divided by 10 (one digit, may be "7" or "8" or "9" or blank);
- cc = CCT of LED divided by 100 (two characters, may be a value of maximum 40 or "MC");
- f = Fixture Type (may be "SD WGS" or "CTR WGS" or blank);
- g = Number of LED module's generation (may be "1");
- s = Commercial suffix for commercial purposes (optional)

## Additional information:

This certificate replaces previous certificate no. ENEC-02242-P2-A1 issued on 2021-12-06, due to:

- Change factory address

---

## Certification Body

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this License, in accordance with the ENEC Requirements. The Designated License holder is entitled to use the ENEC 15 Mark (as shown in annex 1) for the Certified Product manufactured at the production site(s) identified above in accordance with the ENEC Mark Service Agreement including without limitation the ENEC Mark Testing and Certification Services Service Terms. Only those Products bearing the ENEC Mark should be considered as being covered by UL's ENEC Mark Service. This License shall remain valid unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this License is amended or withdrawn prior the Date of Withdrawal of conflicting Standard(s).



# Annex 1 to License No.

## ENEC-02242-P2-A2

### Annex of the form of the Mark



15 is the identification number of the Certification Body

Size of the mark:

The size of the mark may be reduced on the condition that it remains legible and that the ratio  $b/a=1,7$  is kept.

---

#### Certification Body

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this License, in accordance with the ENEC Requirements. The Designated License holder is entitled to use the ENEC 15 Mark (as shown in annex 1) for the Certified Product manufactured at the production site(s) identified above in accordance with the ENEC Mark Service Agreement including without limitation the ENEC Mark Testing and Certification Services Service Terms. Only those Products bearing the ENEC Mark should be considered as being covered by UL's ENEC Mark Service. This License shall remain valid unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this License is amended or withdrawn prior the Date of Withdrawal of conflicting Standard(s).

