


ENEC License

License

ENEC-04756-M2

Issue date

2025-03-03



This is to acknowledge that

SIGNIFY NETHERLANDS B.V.

HIGH TECH CAMPUS 48 EINDHOVEN 5656 AE NETHERLANDS

has had

Built-in LED Module

Main series: Fortimo SLM C (z)(cc) (d) (m) L(ee) (s) G(i) (a)

See page 3 for additional Information

evaluated and meets the requirements of the standard

EN IEC 62031:2020, EN IEC 62031:2020/A11:2021

Test Report Nos. 4791109019-2 issued on 2025-02-26

Certification Manager

Thomas Wilson

**UL International Demko A/S, Borupvang 5A, 2750 Ballerup, Denmark,
Tel. +45 44 85 65 65**

See UL Product iQ® at <https://iq.ulprospector.com> for additional information.

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this License, in accordance with the ENEC Requirements. The Designated License holder is entitled to use the ENEC 15 Mark (as shown in annex 1) for the Certified Product manufactured at the production site(s) identified above in accordance with the ENEC Mark Service Agreement including without limitation the ENEC Mark Testing and Certification Services Service Terms. Only those Products bearing the ENEC Mark should be considered as being covered by UL's ENEC Mark Service. This License shall remain valid unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this License is amended or withdrawn prior the Date of Withdrawal of conflicting Standard(s).

ENEC LICENSE

TECHNICAL DETAILS

Production site(s)

Trademark



Ratings

SELV input, I_{max} 4140 mA === V_{max} 55 V

Maximum ratings of the series:

CoB Type (Die matrix)	Diameter of LES of CoB [mm]	CCT [K]	DC Current [mA]	Power [W]	Power Density/LES of CoB [W/mm ²]	t _c [°C]
1309	15	≤ 4000	1000 (V _{f tot} 40V)	40	0,23	105
1319	23	≤ 4000	2000 (V _{f tot} 40V)	80	0,19	105
1201	6,5	≤ 5000	230 (V _{f tot} 41V)	9,4	0,28	105
1202	6,5	≤ 5000	460 (V _{f tot} 41V)	18,9	0,57	105
1202	6,5	≤ 5000	460 (V _{f tot} 41V)	18,9	0,57	105
1203	9,8	≤ 5000	690 (V _{f tot} 41V)	28,3	0,38	105
1203	9	≤ 5000	690 (V _{f tot} 41V)	28,3	0,44	105
1204	9,8	≤ 5000	920 (V _{f tot} 41V)	37,7	0,50	105
1204	9	≤ 5000	920 (V _{f tot} 41V)	37,7	0,59	105
1205	14,5	≤ 5000	1150 (V _{f tot} 41V)	47,2	0,29	105
1205	13	≤ 5000	1150 (V _{f tot} 41V)	47,2	0,36	105
1206	14,5	≤ 5000	1380 (V _{f tot} 41V)	56,6	0,34	105
1206	13	≤ 5000	1380 (V _{f tot} 41V)	56,6	0,43	105
1208	14,5	≤ 5000	1840 (V _{f tot} 41V)	75,4	0,46	105
1208	15	≤ 5000	1840 (V _{f tot} 41V)	75,4	0,43	105

CoB Type (Die matrix)	Diameter of LES of CoB [mm]	CCT [K]	DC Current [mA]	Power [W]	Power Density/LES of CoB [W/mm ²]	t _c [°C]
1210	14,5	≤ 5000	2300 (V _{f tot} 41V)	94,3	0,57	105
1211	22	≤ 5000	2530 (V _{f tot} 41V)	103,7	0,27	105
1211	18,5	≤ 5000	2530 (V _{f tot} 41V)	103,7	0,39	105
1212	22	≤ 5000	2760 (V _{f tot} 41V)	113,2	0,30	105
1216	22	≤ 5000	3680 (V _{f tot} 41V)	150,9	0,40	105
1216	23	≤ 5000	3680 (V _{f tot} 41V)	150,9	0,36	105
1812	22	≤ 5700	2760 (V _{f tot} 55V)	151,8	0,39	105
1818	22	≤ 5700	4140 (V _{f tot} 55V)	227,7	0,588	105

Type / model	Rated current max(mA)	Risk Group 1 Current (mA)
Fortimo SLM C 940 (d) (m) L23 2828 G(i) (a) (m=1319)	2000mA	≤1650mA
Fortimo SLM C 940 (d) (m) L15 2024 G(i) (a) (m=1309)	1000mA	≤734mA

CoB Type (Gen8 HE)											
CoB Type (Die matrix)	1201	1202	1203	1204	1205	1206	1208	1210	1211	1212	1216
Maximum currents for RG1 [mA]	zcc=840	163	325	488	650	813	975	1300	1625	1788	1950
	zcc=940	168	335	503	670	838	1005	1340	1675	1843	2010
	zcc=850	120	240	360	480	600	720	960	1200	1320	1440
	zcc=950	120	240	360	480	600	720	960	1200	1320	1440

CoB Type (Gen8)											
CoB Type (Die matrix)	1201	1202	1203	1204	1205	1206	1208	1210	1211	1212	1216
Maximum currents for RG1 [mA]	zcc=757	125	250	375	500	625	750	1000	1250	1375	1500
	zcc=857	125	250	375	500	625	750	1000	1250	1375	1500
	zcc=940	125	250	375	500	625	750	1000	1250	1375	1500

CoB Type (Gen8) con't			
CoB Type (Die matrix)		1812	1818
Maximum currents for RG1 [mA]	zcc=757	1500	2250
	zcc=857	1500	2250
	zcc=940	1500	2250

Additional Information

The report was revised to include technical modifications.
This certificate replaces previous certificate no. ENEC-04756-M1 issued on 2024-08-22 due to:

- Add G8 non-HE models (lower power density than original models)
- Update Annex 2.
- Add marking plate.
- Update product key and ratings

See test report for details

Models (continued from page 1)

Series:

Main series: Fortimo SLM C (z)(cc) (d) (m) L(ee) (s) G(i) (a)

Where:

(z) = CRI divided by 10 (may be blank when d = "CED", or one digit, may be "7", "8", or "9")

(cc) = CCT divided by 100 (two digits or six characters (or blank when d = "CED"), may be a value between 22 and 57 (or "27-865" or "27-965" (when d = "TW")))

(d) = Flavour of light (two or three characters, may be "Px (x could be W, C, S, A or any character)" or "CW" or "FPR" or "FWW" or "FLS" or "FVF" or "FIS" or "CED" or "TW" or blank)

(m) = Die matrix (four digits, example 1216 chip configuration = 12 chips in series per string & 16 strings in parallels, (or blank when d = "CED"))

(ee) = Diameter of the Light Emitting Surface (LES) in millimeter (one or two digits, example 23 LES dimensions = 23mm)

(s) = PCB size in mm (four digits, example 2828: CoB dimension = 28mm × 28mm)

(i) = Number of generation of CoB (one digit, may be "8")

(a) = Suffix for commercial purposes (optional).

*each of the brackets in product key are optional

ENEC LICENSE FORM OF THE ENEC MARK



15 is the identification number of the Certification Body

Size of the mark:

The size of the mark may be reduced on the condition that it remains legible and that the ratio $b/a=1,7$ is kept.