

# PHILIPS

## CertaDrive

### LED Transformers



## Datasheet

### Economic LED Transformer 30W 24VDC G2

9290 038 81580

Philips full-electronic constant voltage Economic LED Transformers are designed to operate 24VDC LED solutions used in general built-in and independent applications such as non-center piece lighting, retail display lighting and linear accent lighting. They are specifically designed to ensure good performance with high cost-effectiveness.

#### Features

- Built-in and independent use for Insulation Class II applications
- Stable output voltage
- Wide ambient temperature range
- Protection against overpower and overvoltage
- Output short-circuit shutdown feature with automatic restart

#### Benefits

- SELV operating voltages, ensuring safety even if wiring or LED boards become damaged
- Energy savings through high efficiency
- High robustness, offering peace of mind and lower maintenance costs
- Easy to design-in and install with parallel wiring
- Global approvals

#### Application

- Retail display lighting
- Shelf lighting
- Cove lighting
- Façade accent lighting

## Logistical data

Specification item	Value
Product name	Economic LED Transformer 30W 24VDC G2
Logistic code 12NC	9290 038 81580
Pieces per box	80
Weight	86 gram

## Electrical input data

Specification item	Value	Unit	Condition
Rated input voltage range	220...240	V <sub>ac</sub>	Performance range
Rated input voltage	230	V <sub>ac</sub>	
Rated input frequency	50...60	Hz	Performance range
Rated input current	0.2	A	@ rated output power @ rated input voltage
Rated input power	36.0	W	@ rated output power @ rated input voltage
Power factor	0.9C		@ rated output power @ rated input voltage
Total harmonic distortion	20	%	@ rated output power @ rated input voltage
Efficiency	87.0	%	@ rated output power @ rated input voltage
Input voltage AC	198...264	V <sub>ac</sub>	Operational range
Input frequency AC	47...63	Hz	Operational range
Isolation input to output	SELV		

## Electrical output data


Specification item	Value	Unit	Condition
Regulation method	Constant Voltage		
Output voltage	24	V <sub>dc</sub>	Output voltage range: 22.8 ... 25.2VDC @ output current range 0.75 ... 1.25A
Output current	62.5...1250	mA	
Output voltage ripple	≤ 10	%	
Output power	1.5...30.0	W	
Line regulation	≤ 3	%	
Load regulation	≤ 5	%	
Turn-on delay	≤ 0.5	s	
Output voltage rise time	≤ 100	ms	

## Control interfaces

Specification item	Value	Unit	Condition
Control method	Fixed		

## Wiring and Connections

Specification item	Value	Unit	Type
Input wire cross-section	0.75...1.5 / 18...16	mm <sup>2</sup> / AWG	solid / stranded wire. Up to 2.5mm <sup>2</sup> for built in application only.
Input wire strip length	8...10	mm	
Output wire cross-section	0.5...1.5 / 20...16	mm <sup>2</sup> / AWG	solid / stranded wire
Output wire strip length	6...10	mm	
Maximum cable length	1	m	Total cable length between driver and LED modules per CISPR15




## Isolation

Insulation per IEC61347-1	Input	Output
Input	-	SELV
Output	SELV	-

## Dimensions and weight

Specification item	Value	Unit	Tolerance (mm)
Length (A1)	135	mm	± 1
Mounting hole distance (A2)	126	mm	± 1
Width (B1)	36	mm	± 0.5
Width (B2)	24	mm	± 0.5
Height (C1)	25	mm	± 0.5
Mounting hole diameter (D1)	4	mm	± 0.5
Weight	86	gram	




## Operational temperatures and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-20...+45	°C	Higher ambient temperature allowed as long as Tcase-max is not exceeded
Tcase-max	85	°C	Maximum temperature measured at Tcase-point
Tcase-life	80	°C	Measured at Tcase-point
Relative humidity	10...90	%	Non-condensing

## Lifetime

Specification item	Value	Unit	Condition
Driver lifetime	30,000	hours	Measured temperature at Tcase-point is Tcase-life. Maximum failures = 10%



Maximum failures = 10%

### Storage temperature and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-20...+85	°C	
Relative humidity	5...95	%	Non-condensing

### Non-programmable features


Specification item	Value		Condition
Open load protection	Yes		
Short circuit protection	Yes		Hiccup mode, automatic recovering
Over power protection	Yes		Automatic recovering
Hot wiring	Yes		No load power < 0.5W
Suitable for fixtures with protection class	II		per IEC60598

## Inrush current

Specification item	Value	Unit	Condition
Inrush current	20	A	Input voltage 230V
Inrush peak width	15	μs	Input voltage 230 V, measured at 50% height
Drivers / MCB 16A type B @230V AC	≤ 80	pcs	Input voltage 230V

Please refer to the driver design in guide if you use other MCB-types.

If several mini circuit breakers are used directly side-by-side (without distance pieces) a correction factor of 80% has to be applied to the rated current



## Driver touch current / protective conductor current / earth leakage current

Specification item	Value	Unit	Condition
Typical Touch Current (ins. Class II)	0.7	mA peak	. LED module contribution not included

## Surge immunity

Specification item	Value	Unit	Condition
Mains surge immunity (diff. mode)	1	kV	L-N acc. IEC61000-4-5. 2 Ohm


## Application Info (Approbation)

Specification item	Value
Approval marks and Certifications	CB / CCC / CE / SELV
Ingress Protection classification (IP)	20
Application	Indoor Constant Voltage
Mounting Type	Built-in / Independent

## Graphs


### Operating window

---




### Power factor versus output power

---




### Efficiency versus output power

---



## THD versus output power

---



©2025 Signify Holding, IBRS 10461, 5600 VB, NL. All rights reserved.  
UK importer address: Signify Commercial UK Limited, 3, Guildford Business Park, GU2 8XG.

The information provided herein is subject to change without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

Date of release: March 17, 2025 v2

[www.philips.com/oem](http://www.philips.com/oem)