

UK Declaration of Conformity

Document No.: FORT-2025-0010

Year in which UKCA Mark was first affixed: 2025

1. Product Range / Model:

Product Range / Model:	NAME: Fortimo SLM COB LED Module DESCRIPTION: LED modules BRAND (optional): PHILIPS / SIGNIFY	
------------------------	---	--

2. Authorized Representative Name & Address:

Signify Commercial UK Limited

Unit 2, Guildford Business Park, Guildford, Surrey, GU2 8XG, UK

3. This declaration of conformity is issued under the sole responsibility of the manufacturer: Signify.

4. Object of the declaration:

Product Code:	The Unique product ID number of all products under the family described above, please refer to the Annex: Specification of the products Product Key: Main series: Fortimo SLM C (z)(cc) (d) (m) L(ee) (s) G(i) (a) Where: z = CRI divided by 10 (may be blank when d = "CED", or one digit, may be "7", "8", or "9"); cc = CCT divided by 100 (two digits or six characters (or blank when d = "CED"), may be a value between 22 and 65 (or "27-865" or "27-965" (when d = "TW"))); d = Flavour of light (two or three characters, may be "Px (x could be W, C, S, A or any character)" or "CW" or "FPR" or "FWW" or "FLS" or "FVF" or "FFS" or "FIS" or "CED" or "TW" or blank); m = Die matrix (four digits, example 1216; chip configuration = 12 chips in series per string & 16 strings in parallels, (or blank when d = "CED")); ee = Diameter of the Light Emitting Surface (LES) in millimeter (one or two digits, example 23; LES dimensions = 23mm); s = PCB size in mm (four digits, example 2828: CoB dimension = 28mm × 28mm); i = Number of generation of CoB (one digit, may be , " 8"); a = Suffix for commercial purposes, may contain a blank (optional). *each of the brackets in product key are optional
---------------	--

5&6. The object of the declaration described above is in conformity with the following relevant UK regulation and with the applicable requirements of the following designated standards and technical specifications:

Electrical Equipment (Safety) Regulations 2016 (SI 2016/1101)

EN IEC 62031:2020 + A11:2021

Ecodesign for Energy-related Products Regulations 2010 (SI 2010/2617)

The Eco design for Energy-Related Products and Energy Information (Lighting Products) Regulations 2021 (SI 2021/1095)

The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012 (SI 2012/3032)

EN IEC 63000:2018

7. Additional information: The product in this declaration is produced under a quality scheme at least in conformity with ISO 9001 or CENELEC permanent documents.

Signed for and on behalf of Signify:**Authorized Representative:****14/01/2026****Guildford****UK****Cameron Wilson**

Authorized Representative

UK&I Signify

UK Declaration of Conformity

Document No.: FORT-2025-0010

Specification of the products:

10NC	12NC	Product Description	Brand (optional)	Product Description (other)
9290038727	929003872780	Fortimo SLM C 930 1309 L15 2024 G8 UHE	PHILIPS /SIGNIFY	930 1309FU8
9290038728	929003872880	Fortimo SLM C 935 1309 L15 2024 G8 UHE	PHILIPS /SIGNIFY	935 1309FU8
9290038729	929003872980	Fortimo SLM C 940 1309 L15 2024 G8 UHE	PHILIPS /SIGNIFY	940 1309FU8
9290038730	929003873080	Fortimo SLM C 930 PW 1309 L15 2024 G8 UHE	PHILIPS /SIGNIFY	930P1309FU8
9290038731	929003873180	Fortimo SLM C 935 PW 1309 L15 2024 G8 UHE	PHILIPS /SIGNIFY	935P1309FU8
9290038732	929003873280	Fortimo SLM C 940 PW 1309 L15 2024 G8 UHE	PHILIPS /SIGNIFY	940P1309FU8
9290048691	929004869101	Fortimo SLM C 930 1313 L19 2828 G8 UHE	PHILIPS /SIGNIFY	930 1313FU8
9290048692	929004869201	Fortimo SLM C 935 1313 L19 2828 G8 UHE	PHILIPS /SIGNIFY	935 1313FU8
9290048693	929004869301	Fortimo SLM C 940 1313 L19 2828 G8 UHE	PHILIPS /SIGNIFY	940 1313FU8
9290048694	929004869401	Fortimo SLM C 930 PW 1313 L19 2828 G8 UHE	PHILIPS /SIGNIFY	930P1313FU8
9290048695	929004869501	Fortimo SLM C 935 PW 1313 L19 2828 G8 UHE	PHILIPS /SIGNIFY	935P1313FU8
9290048696	929004869601	Fortimo SLM C 940 PW 1313 L19 2828 G8 UHE	PHILIPS /SIGNIFY	940P1313FU8
9290048729	929004872901	Fortimo SLM C 927 PA 1319 L23 2828 G8 UHE	PHILIPS /SIGNIFY	927A1319FU8
9290038733	929003873380	Fortimo SLM C 930 1319 L23 2828 G8 UHE	PHILIPS /SIGNIFY	930 1319FU8
9290038734	929003873480	Fortimo SLM C 935 1319 L23 2828 G8 UHE	PHILIPS /SIGNIFY	935 1319FU8
9290038735	929003873580	Fortimo SLM C 940 1319 L23 2828 G8 UHE	PHILIPS /SIGNIFY	940 1319FU8
9290038736	929003873680	Fortimo SLM C 930 PW 1319 L23 2828 G8 UHE	PHILIPS /SIGNIFY	930P1319FU8
9290038737	929003873780	Fortimo SLM C 935 PW 1319 L23 2828 G8 UHE	PHILIPS /SIGNIFY	935P1319FU8
9290038738	929003873880	Fortimo SLM C 940 PW 1319 L23 2828 G8 UHE	PHILIPS /SIGNIFY	940P1319FU8
9290048685	929004868501	Fortimo SLM C 930 1304 L09 1313 G8N UHE	PHILIPS /SIGNIFY	930 1304NU8
9290048686	929004868601	Fortimo SLM C 935 1304 L09 1313 G8N UHE	PHILIPS /SIGNIFY	935 1304NU8

UK Declaration of Conformity

Document No.: FORT-2025-0010

10NC	12NC	Product Description	Brand (optional)	Product Description (other)
9290048687	929004868701	Fortimo SLM C 940 1304 L09 1313 G8N UHE	PHILIPS /SIGNIFY	940 1304NU8
9290048688	929004868801	Fortimo SLM C 930 PW 1304 L09 1313 G8N UHE	PHILIPS /SIGNIFY	930P1304NU8
9290048689	929004868901	Fortimo SLM C 935 PW 1304 L09 1313 G8N UHE	PHILIPS /SIGNIFY	935P1304NU8
9290048690	929004869001	Fortimo SLM C 940 PW 1304 L09 1313 G8N UHE	PHILIPS /SIGNIFY	940P1304NU8
9290048728	929004872801	Fortimo SLM C 927 PA 1309 L15 1919 G8N UHE	PHILIPS /SIGNIFY	927A1309NU8
9290048499	929004849901	Fortimo SLM C 930 1309 L15 1919 G8N UHE	PHILIPS /SIGNIFY	930 1309NU8
9290048500	929004850001	Fortimo SLM C 935 1309 L15 1919 G8N UHE	PHILIPS /SIGNIFY	935 1309NU8
9290048501	929004850101	Fortimo SLM C 940 1309 L15 1919 G8N UHE	PHILIPS /SIGNIFY	940 1309NU8
9290048502	929004850201	Fortimo SLM C 930 PW 1309 L15 1919 G8N UHE	PHILIPS /SIGNIFY	930P1309NU8
9290048503	929004850301	Fortimo SLM C 935 PW 1309 L15 1919 G8N UHE	PHILIPS /SIGNIFY	935P1309NU8
9290048504	929004850401	Fortimo SLM C 940 PW 1309 L15 1919 G8N UHE	PHILIPS /SIGNIFY	940P1309NU8