Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: PHILIPS

Supplier's address: Customer Care Philips, I.B.R.S./C.C.R.I. /Numéro 10461, 5600VB Eindhoven, NL

Model identifier: 929002959206

Type of light source:

Lighting technology used:	LED	Non-directional or directional:	NDLS
Light source cap-type (or other electric interface)	NA		
Mains or non-mains:	NMLS	Connected light source (CLS):	No
Colour-tuneable light source:	No	Envelope:	-
High luminance light source:	No		
Anti-glare shield:	No	Dimmable:	Yes

Product parameters

Parameter	Value	Parameter	Value
General product parameters:			
Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer	29	Energy efficiency class	C
Useful luminous flux (ϕuse), indicating if it refers to the flux in a sphere (360º), in a wide cone (120º) or in a narrow cone (90º)	5 146 in Sphere (360°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	3 000
On-mode power (P_{on}), expressed in W	29,0	Standby power (P_{sb}), expressed in W and rounded to the second decimal	0,00
Networked standby power (P_{net}) for CLS, expressed in W and rounded to the second decimal	-	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	90
Outer dimensions without separate control gear, lighting control — Height	6	Spectral power distribution in the range 250 nm to 800 nm, at full-load	See image in last page
Outer dimensions without separate control gear, lighting control — Width	350		
Outer dimensions without separate control gear, lighting control — Depth	350		

parts and non-lighting control parts, if any (millimetre)				
Claim of equivalent power[(a)]		-	If yes, equivalent power (W)	-
			Chromaticity coordinates (x and y)	0,436 0,402
Parameters for LED and OLED light sources:				
R9 colour rendering index value		50	Survival factor	0,90
the lumen maintenance factor		0,96		

[(a)] '-' : not applicable;

[(b)] '-' : not applicable;


1.00
0.90
0.80
0.70
0.60
0.50
0.40
0.30
0.20
0.10
0.00
Relative intensity
250
350
450
550
650
750
wavelength [nm]

Model placed on the Union market from 23/03/2023.

EPREL registration number: 1500759

https://eprel.ec.europa.eu/qr/1500759

Supplier: Signify Netherlands B.V. (Manufacturer) **Website:** www.signify.com

Customer care service:

Name: Customer Care Philips **Website:** www.philips.com/lighting

Email: EPREL.PhilipsLighting@Signify.com **Phone:** 00800 744 547 75

Address:
I.B.R.S./C.C.R.I. /Numéro 10461
5600VB Eindhoven
Netherlands