

# Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

**Supplier's name or trade mark:** PHILIPS

**Supplier's address:** Customer Care Philips, I.B.R.S./C.C.R.I. /Numéro 10461, 5600VB Eindhoven, NL

**Model identifier:** 8718291689188

## Type of light source:

|                                                     |       |                                 |        |
|-----------------------------------------------------|-------|---------------------------------|--------|
| Lighting technology used:                           | MH    | Non-directional or directional: | DLS    |
| Light source cap-type (or other electric interface) | GX8.5 |                                 |        |
| Mains or non-mains:                                 | NMLS  | Connected light source (CLS):   | No     |
| Colour-tuneable light source:                       | No    | Envelope:                       | Second |
| High luminance light source:                        | No    |                                 |        |
| Anti-glare shield:                                  | Yes   | Dimmable:                       | No     |


## Product parameters

| Parameter                                                                                                                                      | Value                      | Parameter                                                                                                                                                  | Value                                                                   |
|------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------|
| <b>General product parameters:</b>                                                                                                             |                            |                                                                                                                                                            |                                                                         |
| Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer                                                                  | 40                         | Energy efficiency class                                                                                                                                    | G                                                                       |
| Useful luminous flux ( $\phi_{use}$ ), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°) | 1 350 in Narrow cone (90°) | Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set | 3 000                                                                   |
| On-mode power ( $P_{on}$ ), expressed in W                                                                                                     | 39,1                       | Standby power ( $P_{sb}$ ), expressed in W and rounded to the second decimal                                                                               | 0,00                                                                    |
| Networked standby power ( $P_{net}$ ) for CLS, expressed in W and rounded to the second decimal                                                | -                          | Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set                                                         | 90                                                                      |
| Outer dimensions without separate control gear, lighting control                                                                               | Height                     | 95                                                                                                                                                         | Spectral power distribution in the range 250 nm to 800 nm, at full-load |
|                                                                                                                                                | Width                      | 111                                                                                                                                                        |                                                                         |
|                                                                                                                                                | Depth                      | 111                                                                                                                                                        |                                                                         |
|                                                                                                                                                |                            |                                                                                                                                                            | See image in last page                                                  |

|                                                           |        |                                                                    |                |
|-----------------------------------------------------------|--------|--------------------------------------------------------------------|----------------|
| parts and non-lighting control parts, if any (millimetre) |        |                                                                    |                |
| Claim of equivalent power <sup>(a)</sup>                  | -      | If yes, equivalent power (W)                                       | -              |
|                                                           |        | Chromaticity coordinates (x and y)                                 | 0,434<br>0,398 |
| <b>Parameters for directional light sources:</b>          |        |                                                                    |                |
| Peak luminous intensity (cd)                              | 36 000 | Beam angle in degrees, or the range of beam angles that can be set | 10             |

(a)-' : not applicable;

(b)-' : not applicable;



Model placed on the Union market from 01/09/2021.



**EPREL registration number:** 473279

<https://eprel.ec.europa.eu/qr/473279>

**Supplier:** Signify Netherlands B.V. (Manufacturer)

**Website:** [www.signify.com](http://www.signify.com)

**Customer care service:**

**Name:** Customer Care Philips

**Website:** [www.philips.com/lighting](http://www.philips.com/lighting)

**Email:** [EPREL.PhilipsLighting@Signify.com](mailto:EPREL.PhilipsLighting@Signify.com)

**Phone:** 00800 744 547 75

**Address:**

I.B.R.S./C.C.R.I. /Numéro 10461

5600VB Eindhoven

Netherlands