


PHILIPS

Fortimo

LED

Fortimo LED CS 350 HF
8xx LV6



Datasheet

Fortimo Circular Shape

The Fortimo LED Circular Shape (CS) is a unique portfolio which offers a combination of energy efficiency, homogenous lighting, long lifetime and design flexibility, making them an important component in many lighting applications. Its form factor makes it easy to design-in and handle in production. Thanks to the availability of three different dimensions, a wide range of needs is covered for our customers.

Key features and benefits

- Typical module efficiency of 200 Lm/W (at 4000K CRI80)
- CRI90 High Efficiency typical performance of 189 Lm/W (at 4000K CRI90)
- Long lifetime: >72,000 hours
- Excellent color consistency of 3 SDCM
- Typical output per dimension available:
 - 220 mm: 2500lm
 - 350 mm: 5500lm
 - 540 mm: 4125lm
- CCTs available: 3000K, 4000K
- CRI >80 & >90 (Based on high efficiency technology)
- Available in Low Voltage (LV)
- Available in front connector (FC)
- PCB thickness of 1.6mm
- Available dimensions: 220mm / 350mm / 540mm / 540Dmm (includes cutout for sensor)
- Wide temperature (Tc) range -40°C to +85°C
- Five-year system warranty (when paired with Xitanium LED drivers)

March 2023



Ordering data

Commercial product name	12NC	EPREL registration #	Box quantity
Fortimo LED CS 350 HF 830 LV6	9290 029 58806	1500757	20
Fortimo LED CS 350 HF 840 LV6	9290 029 59006	1500758	20

Drive currents

Parameter	Nominal*	Life**	Max***	Unit
Fortimo LED CS 350 HF 8xx LV6	725	4800	4800	mA

Module temperatures

Parameter	Nominal*	Life**	Max***	Unit
T _c (case temperature at T _c point)	35	65	85	°C

* Nominal value at which typical performance is specified

** Value at which life time is specified

*** Maximum value for safe operation, do not operate above this value

Optical characteristics - table per color (CCT)


Fortimo LED CS 350 HF 830 LV6

Parameter	Min	Typ	Max	Unit
Luminous flux	4940	5090	5420	lm
Efficacy	178	186	210	lm/W
Correlated color temperature (CCT)		3000		K
Color coordinates (CIEx, CIEy)		(0.433, 0.400)		-
Color consistency			3	SDCM
CRI	80			
R9	0			
Photobiological safety			RG1 unlimited	



Measurement precision $\pm 5\%$ for the flux data and $\pm 6\%$ for the efficacy data. Measurement precision for color coordinates ± 0.005 . Measurement precision for CRI ± 1.5 .

Operation point	830	lm	lm/W
80% I-nom 580mA	Tc 25 °C	4142	191
	Tc-nom 35 °C	4093	189
	Tc-max 85 °C	3797	179
I-nom 725mA	Tc 25 °C	5152	189
	Tc-nom 35 °C	5090	186
	Tc-max 85 °C	4722	177
I-max 4800mA	Tc 25 °C	30159	152
	Tc-nom 35 °C	29788	150
	Tc-max 85 °C	27570	142




Fortimo LED CS 350 HF 840 LV6

Parameter	Min	Typ	Max	Unit
Luminous flux	5320	5500	6050	lm
Efficacy	191	201	234	lm/W
Correlated color temperature (CCT)		4000		K
Color coordinates (CIEx, CIEy)		(0.381, 0.377)		-
Color consistency			3	SDCM
CRI	80			
R9	0			
Photobiological safety			RG1 unlimited	



Measurement precision $\pm 5\%$ for the flux data and $\pm 6\%$ for the efficacy data. Measurement precision for color coordinates ± 0.005 . Measurement precision for CRI ± 1.5 .

Operation point	840	lm	lm/W
80% I-nom 580mA	Tc 25 °C	4476	206
	Tc-nom 35 °C	4420	205
	Tc-max 85 °C	4094	193
I-nom 725mA	Tc 25 °C	5570	204
	Tc-nom 35 °C	5500	201
	Tc-max 85 °C	5094	191
I-max 4800mA	Tc 25 °C	32857	165
	Tc-nom 35 °C	32433	163
	Tc-max 85 °C	29982	153



Electrical characteristics

Fortimo LED CS 350 HF 830 LV6

Parameter	Min	Typ	Max	Unit
Forward voltage	35.6	37.7	38.4	V
Power consumption	25.8	27.3	27.8	W = kWh/1000h
Number of modules in series per chain			1	
Number of modules in parallel			1	

Measurement precision for Vf +/- 3%. Measurement precision for power +/- 3.3%

Fortimo LED CS 350 HF 840 LV6


Parameter	Min	Typ	Max	Unit
Forward voltage	35.6	37.7	38.4	V
Power consumption	25.8	27.3	27.8	W = kWh/1000h
Number of modules in series per chain			1	
Number of modules in parallel			1	

Measurement precision for Vf +/- 3%. Measurement precision for power +/- 3.3%

Tuning information


Flux and efficacy versus current (at Tc nominal)

I [mA]	Flux [%]	Efficacy [%]
4800	590	81
2762	356	88
725	100	100
580	80	101
362	50	103



Flux and efficacy versus temperature at Tc (at I nominal)

Tc [°C]	Flux [%]	Efficacy [%]
85	93	94
35	100	100
25	101	101
0	104	103




Lumen maintenance

Operation point	Lumen maintenance x 1000 hours	L70			L80			L90		
		B50	B20	B10	B50	B20	B10	B50	B20	B10
80% I-nom 580mA	Tc 25°C	>72	>72	>72	>72	>72	>72	>72	>72	>72
	Tc-nom 35°C	>72	>72	>72	>72	>72	>72	>72	>72	>72
	Tc-life 65°C	>72	>72	>72	>72	>72	>72	68	65	66
I-nom 725 mA	Tc 25°C	>72	>72	>72	>72	>72	>72	>72	>72	>72
	Tc-nom 35°C	>72	>72	>72	>72	>72	>72	>72	>72	>72
	Tc-life 65°C	>72	>72	>72	>72	>72	>72	65	64	63
I-life 4800 mA	Tc=25°C	>72	>72	>72	>72	>72	>72	>72	>72	>72
	Tc-nom 35°C	>72	>72	>72	>72	>72	>72	69	68	67
	Tc-life 65°C	>72	>72	>72	>72	>72	>72	46	45	44

Lifetime

Parameter	Value	Unit
M70F50 nominal	>72000	hours
M70F50 life	>72000	hours

Performance Window




Wiring

Specification item	Value	Unit	Condition
Input wire cross-section	0.25...0.75	mm ²	solid wire
	18...24	AWG	solid wire
Input wire strip length	7.5...8.5	mm	
Input wire cross-section	0.33...0.5	mm ²	stranded wire
	20...22	AWG	stranded wire
Input wire strip length	7.5...8.5	mm	



Mechanical characteristics

Parameter	Min	Typ	Max	Unit
Length	339.75	340	340.25	mm
Width	339.75	340	340.25	mm
Height PCB		1.6		mm
Height	5.9	6.1	6.3	mm
Product mass		320		gram



Absolute ratings

Parameter	Min	Max	Unit
Current through the LED module (I-max)		4800	mA
Case temperature (Tc-max)		85	°C
ESD (direct contact)	8		kV
Working voltage		350	V _{dc}

Application information

Certificates and Standards

CE
ENEC
ENEC+
UL

Environmental

RoHS/REACH

Application

Dimming	Yes
Suitable for Damp Locations	



© 2023 Signify Holding, IBRS 10461, 5600VB, NL. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

www.philips.com/oem

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.
UK importer address: Signify Commercial UK Limited, 3 Guildford Business Park, GU2 8XG

21/03/2023