

PHILIPS

Fortimo

LED

Fortimo LED-R 2ft MF 9xx
FC LV5



Datasheet

Fortimo LED-R 2ft MF 9xx FC LV5

The Fortimo LED-R LED modules are designed together with the BJB OptiLine Louvres. These modules and optics are perfectly fitted for each other which leads to a high performance on both efficiency and uniformity. Besides that, installation in a fixture is extremely easy due to the one-click-system which allows installation without screwing. The range of modules is very complete and offers a solution for many different applications and includes regular CRI80, CRI90 High Efficiency, FlexTune and BioUp CED.

Key features and benefits

- High typical module efficacy
- Long life time: >50,000 hours
- Excellent color consistency of 3 SDCM
- Available in 2700K, 3000K and 4000K
- 1ft and 2ft lengths
- Good light quality: CRI90, R9 >50
- Extremely easy to install in combination with BJB OptiLine Louvres
- Available in High Voltage (HV) and Low Voltage (LV)
- Five year system warranty when paired with Xitanium drivers

May 2022



Ordering data

Commercial product name	EOC	12NC	EPREL registration #	Box quantity
Fortimo LED-R 2ft MF 927 FC LV5	8719514 447851 00	9290 034 05806	1227077	110
Fortimo LED-R 2ft MF 930 FC LV5	8719514 447875 00	9290 034 05906	1227089	110
Fortimo LED-R 2ft MF 940 FC LV5	8719514 447899 00	9290 034 06006	1227060	110

These LED-modules are designed to be used with BJB LED OptiLine Louvre Optcs.
Contact your Signify sales representative or BJB for more info.

9290 029 36906 Medium beam lens 1ft (35.306.1001.85)
9290 029 37006 Wide beam lens 1ft (35.306.1002.85)
9290 029 37406 black raster 1ft (35.306.2001.80)
9290 029 37306 white raster 1ft (35.306.2001.50)
9290 029 36806 black raster 2ft (35.312.2001.80)
9290 029 36706 white raster 2ft (35.312.2001.50)

Drive currents

Parameter	Nominal*	Life**	Max***	Unit
Fortimo LED-R 2ft MF 9xx FC LV5	392	600	800	mA

Module temperatures

Parameter	Nominal*	Life**	Max***	Unit
T _c (case temperature at T _c point)	45	75	85	°C

* Nominal value at which typical performance is specified

** Value at which life time is specified

*** Maximum value for safe operation, do not operate above this value


Optical characteristics - table per color (CCT)

Fortimo LED-R 2ft MF 927 FC LV5

Parameter	Min	Typ	Max	Unit
Luminous flux	1930	1990	2150	lm
Efficacy	144	150	167	lm/W
Correlated color temperature (CCT)		2700		K
Color coordinates (CIEx, CIEy)		(0.458, 0.408)		-
Color consistency			3	SDCM
CRI	90			
R9	50			
Photometric code		927/339		
Photobiological safety			RG1 unlimited	

Measurement precision $\pm 5\%$ for the flux data and $\pm 6\%$ for the efficacy data. Measurement precision for color coordinates ± 0.005 . Measurement precision for CRI ± 1.5 .

Operation point	927	lm	lm/W
80% I-nom 314mA	Tc 25 °C	1647	156
	Tc-nom 45 °C	1608	154
	Tc-max 85 °C	1512	147
I-nom 392mA	Tc 25 °C	2038	153
	Tc-nom 45 °C	1990	150
	Tc-max 85 °C	1870	143
I-max 800mA	Tc 25 °C	3969	138
	Tc-nom 45 °C	3874	136
	Tc-max 85 °C	3635	129




Fortimo LED-R 2ft MF 930 FC LV5

Parameter	Min	Typ	Max	Unit
Luminous flux	2000	2060	2220	lm
Efficacy	149	155	173	lm/W
Correlated color temperature (CCT)		3000		K
Color coordinates (CIEx, CIEy)		(0.435, 0.400)		-
Color consistency			3	SDCM
CRI	90			
R9	50			
Photometric code		930/339		
Photobiological safety			RG1 unlimited	

Measurement precision $\pm 5\%$ for the flux data and $\pm 6\%$ for the efficacy data. Measurement precision for color coordinates ± 0.005 . Measurement precision for CRI ± 1.5 .

Operation point	930	lm	lm/W
80% I-nom 314mA	Tc 25 °C	1705	162
	Tc-nom 45 °C	1665	159
	Tc-max 85 °C	1565	152
I-nom 392mA	Tc 25 °C	2110	158
	Tc-nom 45 °C	2060	155
	Tc-max 85 °C	1936	148
I-max 800mA	Tc 25 °C	4109	143
	Tc-nom 45 °C	4010	141
	Tc-max 85 °C	3763	134




Fortimo LED-R 2ft MF 940 FC LV5

Parameter	Min	Typ	Max	Unit
Luminous flux	2130	2200	2380	lm
Efficacy	159	166	185	lm/W
Correlated color temperature (CCT)		4000		K
Color coordinates (CIE _x , CIE _y)		(0.381, 0.380)		-
Color consistency			3	SDCM
CRI	90			
R9	50			
Photometric code		940/339		
Photobiological safety			RG1 unlimited	

Measurement precision $\pm 5\%$ for the flux data and $\pm 6\%$ for the efficacy data. Measurement precision for color coordinates ± 0.005 . Measurement precision for CRI ± 1.5 .

Operation point	940	lm	lm/W
80% I-nom 314mA	Tc 25 °C	1821	173
	Tc-nom 45 °C	1778	170
	Tc-max 85 °C	1672	162
I-nom 392mA	Tc 25 °C	2253	169
	Tc-nom 45 °C	2200	166
	Tc-max 85 °C	2068	158
I-max 800mA	Tc 25 °C	4389	153
	Tc-nom 45 °C	4284	150
	Tc-max 85 °C	4020	143




Electrical characteristics

Parameter	Min	Typ	Max	Unit
Forward voltage	32.8	33.8	34.1	V
Power consumption	12.9	13.2	13.4	W = kWh/1000h
Number of modules in series per chain			1	
Number of modules per chain			2	

Tuning information


Flux and efficacy versus current (at Tc nominal)

I [mA]	Flux [%]	Efficacy [%]
600	149	95
496	125	97
392	100	100
314	81	102
196	51	106



Flux and efficacy versus temperature at Tc (at I nominal)

Tc [°C]	Flux [%]	Efficacy [%]
85	94	95
45	100	100
25	102	102
0	105	103




Lumen maintenance

Operation point	Lumen maintenance x 1000 hours	L70			L80			L90		
		B50	B20	B10	B50	B20	B10	B50	B20	B10
80% Inom=314mA	Tc=25°C	>70	>70	>70	>70	>70	>70	66	64	63
	Tc_nom=45°C	>70	>70	>70	>70	>70	>70	52	51	50
	Tc_life=75°C	>70	>70	>70	>70	>70	>70	38	37	37
Inom=392mA	Tc=25°C	>70	>70	>70	>70	>70	>70	63	61	60
	Tc_nom=45°C	>70	>70	>70	>70	>70	>70	50	49	48
	Tc_life=75°C	>70	>70	>70	>70	>70	>70	36	35	35
Ilife=600mA	Tc=25°C	>70	>70	>70	>70	>70	>70	58	56	56
	Tc_nom=45°C	>70	>70	>70	>70	>70	>70	46	45	44
	Tc_life=75°C	>70	>70	>70	>70	69	68	33	33	32

Lifetime


Parameter	Value	Unit
M70F50 nominal	>70000	hours
M70F50 life	>70000	hours

Performance Window




Wiring

Specification item	Value	Unit	Condition
Input wire cross-section	0.2...0.75	mm ²	solid wire, stranded wire
	18...24	AWG	solid wire, stranded wire
Input wire strip length	7.5...9.5	mm	



Mechanical characteristics

Parameter	Min	Typ	Max	Unit
Length	558.9	559.2	559.5	mm
Width	19.8	20	20.6	mm
Height PCB		1.6		mm
Height Total		4.3		mm
Product mass		50		gram



Absolute ratings

Parameter	Min	Max	Unit
Current through the LED module (I-max)		800	mA
Case temperature (Tc-max)		85	°C
ESD (direct contact)	8		kV
Working voltage		120	V _{dc}

Application information

Certificates and Standards

CE
ENEC
ENEC+
cULus

Application

Overheating protection	no
Dimming	Yes



© 2022 Signify Holding, IBRS 10461, 5600VB, NL. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

www.philips.com/oem

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.
UK importer address: Signify Commercial UK Limited, 3 Guildford Business Park, GU2 8XG

17/05/2022