

 **signify**

**interact**



LCN41x0/05



LCN41x0/15

Specification Sheet

# **LCN4120/05, LCN4120/15, LCN4150/05, LCN4150/15 Outdoor Parking Sensor**

The Outdoor Parking Sensor is part of a luminaire-based lighting control system.

# LCN41x0/x5

## Features

- Interact ready
- PIR motion sensor for occupancy detection
- Light sensor for closed loop daylight regulation
- Infrared receiver module for IR remote control
- Zigbee and Bluetooth Low Energy (BLE) transceiver
- Luminaire integration with Zhaga Book 18 connector


## Benefits

- Wireless communication, no extra wiring required
- Easy grouping of luminaires with sensor during setup process
- Supports standalone mode and connection to gateway for energy reporting
- Two lens options for installation heights up to 15 ft (4.6 m) and up to 40 ft (12.2 m)
- Unique 32-bit sensor identifier and encrypted wireless communication prevents interference with other devices

## Applications

Typical application areas are outdoor parking lots and covered parking garages. The LCN4120/x5 sensor is suited for mounting heights from 2.1 to 4.6 m (7 to 15 ft), and LCN4150/x5 is suited for mounting heights from 4.6 to 12.2 m (15 to 40 ft). Sensitivity patterns change according to the mounting height.

## Dimensional drawing



## LED indicator


The sensor features two integrated LEDs (red and yellow) to indicate the functioning of the PIR sensor. The LED light guide is integrated in the service button. The LED color definition is explained below.

Steady red	presence/movement detected
Steady yellow	Sensor is working but no presence/ movement detected
No color	Malfunction or LED indication is disabled by configuration settings

## Connector

The sensor connects to a Zhaga Book 18 4-pin twist and lock socket.

## Wiring diagram



### PIR occupancy detection area


The images below shows the occupancy coverage for the low-bay sensor and the high-bay sensor based on the industry NEMA test.

**Note**  
As PIR based sensing works on the difference between subject's temperature and ambient temperature, the occupancy detection could vary due to clothing and size of the subject. The sensor detection area will decrease when the difference in subject's temperature and ambient temperature is approximately 5 °C or less.


**Note**  
The beam pattern shown is intended solely as a general guide and is not to scale. Sensing capabilities and coverage area depend on many factors including the size, speed and direction of travel of persons and vehicles, sensor mounting height, environmental and site conditions, etc.



LCN4120/x5 LowBay



LCN4150/x5 HighBay



# Specifications

## Physical

Dimensions (h x w)	41.7 x 80.9 mm (1.64 x 3.18 in)
Weight	0.09 kg
Protection	IP66

## Installation height

LCN4120/x5	2.1 to 4.6 m (7 to 15 ft)
LCN4150/x5	4.6 to 12.2 m (15 to 40 ft)

## Environment

Operating temperature	-40 to 55 °C (-40 to 131 °F)
Storage temperature	-40 to 70 °C (-40 to 158 °F)
Humidity operating	20 to 85% (non-condensing)
Humidity storage	10 to 95% (non-condensing)

## Wireless Communication

BLE	protocol 4.2 (5.1 compliant)
BLE range smartphone to sensor	15 m (49 ft)
Zigbee	light link protocol (IEEE 802.15.4)
Zigbee range sensor to sensor	49 m (160 ft)

## Electrical

Supply voltage	9 to 24 Vdc
Power consumption operational	Typ. 4.5 mA at 24 V (108 mW)
Classification	Designed to be built into class I or class II luminaire, plenum rated

## Reliability

Calculated failure rate at nominal supply voltage and 55 °C	300 ppm/1000 h
Estimated lifetime	100 k hours at 55 °C ambient temperature at full load

## Compliances and approvals

Approbations	CE, UKCA, ENEC, UL, FCC
EMC emission	FCC Part 15 - Subpart B ANSI C63.4-2014
EMC immunity	FCC Part 15 - Subpart B
CE standards	Radio equipment directive 2014/53/EU: <ul style="list-style-type: none"> <li>• EN 61347-1:2015 + A1:2021</li> <li>• EN 61347-2-11:2001 + A1:2019</li> <li>• ETSI EN 308328:2019 V2.2.2</li> <li>• ETSI EN 301489-1:2019 V2.2.3</li> <li>• ETSI EN 301489-17:2020 V3.2.4</li> <li>• EN IEC 55015:2019 + A11:2020</li> <li>• EN 61547:2009</li> <li>• EN 62311:2020</li> </ul> <p>Restriction of the use of certain Hazardous Substances in electrical and electronic equipment Directive (RoHS), 2011/65/EU:</p> <ul style="list-style-type: none"> <li>• EN IEC 63000:2018</li> </ul>
UKCA standards	Radio Equipment Regulations 2017: <ul style="list-style-type: none"> <li>• EN 61347-1:2015 + A1:2021</li> <li>• EN 61347-2-11:2001 + A1:2019</li> <li>• ETSI EN 308328:2019 V2.2.2</li> <li>• ETSI EN 301489-1:2019 V2.2.3</li> <li>• ETSI EN 301489-17:2020 V3.2.4</li> <li>• EN IEC 55015:2019 + A11:2020</li> <li>• EN 61547:2009</li> <li>• EN 62311:2020</li> </ul> <p>Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012:</p> <ul style="list-style-type: none"> <li>• EN IEC 63000:2018</li> </ul>



# Ordering data

## For North America

Type	MOQ	Ordering number
LCN4120/05 WH IA Outdoor WL Sensor, low install height, white	1	9137 010 63113
LCN4120/15 BL IA Outdoor WL Sensor, low install height, black	1	9137 010 63313
LCN4150/05 WH IA Outdoor WL Sensor, high install height, white	1	9137 010 63213
LCN4150/15 BL IA Outdoor WL Sensor, high install height, black	1	9137 010 63413

## For the rest of the world/Europe

Type	MOQ	Ordering number
LCN4120/05 WH IA Outdoor WL Sensor, low install height, white	1	9137 010 63103
LCN4120/15 BL IA Outdoor WL Sensor, low install height, black	1	9137 010 63303
LCN4150/05 WH IA Outdoor WL Sensor, high install height, white	1	9137 010 63203
LCN4150/15 BL IA Outdoor WL Sensor, high install height, black	1	9137 010 63403

## Specific Data Notice

This Specific Data Notice applies to the sensors as specified in this product specification/data sheet (the “**Sensor**”) that is part of or works with a Professional System offered by Signify for use in the European Union and supplements and/or corrects the Generic Data Notice For Professional Systems and Services that can be found at: <https://www.signify.com/global/legal/digital-terms/datanotices/en> (the “**Generic Data Notice**”) by providing additional and/or more specific details specific to this Sensor.

Terms starting with a capital in this Specific Data Notice, will have the meaning as attributed thereto in the Generic Data Notice, unless explicitly defined otherwise in this document.

When used in a professional lighting system of Signify in combination with an Interact Wireless Gateway with either the Interact Building Manager or Interact Pro software services the Sensor is capable of generating the Data as specified below<sup>1</sup>:

- Operational Data: energy consumption, failures (of light points and driver), burning hours (read from the driver as per DALI-2 protocol)
- Sensor Data: occupancy state for the last minute as per Zigbee wireless communication protocol

The Product Data generated in this combination is communicated via the gateway to the Interact cloud where these are stored. Product Data is neither stored on the Sensor itself nor on the gateway. Product Data cannot be accessed directly from the Sensor<sup>2</sup> Product Data that is Readily Available Data can be accessed as indicated in the software specification sheet of respectively Interact Building Manager and Interact Pro.

This Specific Data Notice may be changed by Signify from time to time. The current version of this notice will apply and can be obtained at request via the point of contact as indicated in paragraph 7 of the Generic Data Notice.

1. The type and volume and format of Product Data that is actually generated depends on the product and/or software configuration and subscription to the relevant software service.
2. In typical use the connected product is commissioned in which state the on-device generated data cannot be directly accessed to safeguard security.

©2020-2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

All trademarks are owned by Signify Holding or their respective owners.



[Products | Signify](#)