

**PHILIPS**

CT node



## Specification Sheet

# LLC7813

The CT node is a luminaire-based control device that connects your street light to the Signify-supported lighting management systems, such as Interact City.


The CT node uses cellular communication to remotely manage, monitor and control each street light individually.

The CT node controls the street light by switching the mains supply and provides dimming by means of a digital (DALI) or analog (1-10V) interface.



# LLC7813

- The CT node is mounted to the luminaire by twist-locking it onto the 3, 5 or 7-pin NEMA receptacle.
- The CT node provides true plug and play commissioning: it automatically connects to the mobile network, automatically locates itself with the onboard GPS, and automatically uploads its asset data to the lighting management system.
- The CT node works together with certified D4i motion sensor.
- The CT node includes a tilt sensor to get instant notification in case the orientation of the luminaire and/or pole changes significantly.
- The CT Node works with street lights from almost any manufacturer.

## Dimensional drawing



## Wiring diagrams



# Specifications

## Dimensions

Component height	83.6 mm (3.29 in)
Cover height	74.4 mm (2.93 in)
Diameter	88.6 mm (3.49 in)
Weight	0.27 kg (0.6 lb)

## Color

LLC7813	Light Grey (RAL 7035)
---------	-----------------------

## Supply

Mains voltage	120 to 240 Vac -15%/+10%
Mains frequency	50/60 Hz -5%/+5%
Rated current	4A at 120 Vac or 3A at 240 Vac

## Power Consumption

Standby power	0.94 W @ 230V
---------------	---------------

## Control interface

Control method	ON/OFF, 1-10 V, DALI (default)
Protection	Interface is protected against short circuit
Insulation	Class 2, Basic insulation
Load capacity	Maximum 4 LED drivers, up to 4A at 120 Vac or 3A at 240 Vac

## DALI SR interface

Performance requirements DALI	IEC 62386-101 edition 2.0 IEC 62386-103 edition 2.0 IEC 62386-351 edition 1.0
D4i device type	Type A (The D4i specification-Part 351 ensures the Type A device can be used together with Type B device, such as D4i sensor, in a D4i luminaire)
DALI supply	<ul style="list-style-type: none"> <li>DALI master with integrated DALI power supply</li> <li>Suitable for multiple power supplies on a DALI bus</li> </ul>

Supply voltage	Min. 11.5 V, Max. 22 V
Guaranteed supply current	Min. 10 mA
Max. supply current	Max. 30 mA

## Mounting

5-pin plug conform ANSI C136.41

## Connectivity

Technology	2G (GPRS) 4G/5G (LTE Cat M1 bands 3, 8 and 20)
------------	---

## Energy metering

Energy metering device	Inside CT node
Energy meter accuracy	0.5% class conform IEC 62052-11 IEC 62053-21 EN 62052-11/A11 EN 50470-3

## Auto location

Positioning device	Inside CT node
Positioning accuracy	CEP50 $\leq$ 2.5 m

## Luminaire tilt notification

Tilt sensor	Inside CT node
Tilt threshold accuracy	$\pm 5^\circ$
Configurable range	Between 20 and 45°
Default setting	30°

## Lighting control management systems

Interact City, Telensa PLANet

## Light control

Light-sensing device	Inside CT node
Measurement range	Between 5 and 400 lux
Configurable range	Remote configurable light level between 15 and 200 lux
Default settings	Default dusk/dawn level 20/20 lux

### Astronomical clock control

Configurable range	Remote configurable time offset range -120 to 120 minutes, sun elevation angle range -25 to 25°
Default settings	Default dusk/dawn angle 0°/0°

### Surge immunity

Power supply	6 kV/3kA acc. ANSI C136.10
Control surge (diff. mode)	0.5 kV acc. IEC61000-4-5. 40 Ω, 1.2/50 μs, 8/20 μs
Control surge (comm. mode)	1 kV acc. IEC61000-4-5. 40 Ω, 1.2/50 μs, 8/20 μs

### Temperature characteristics

Operating temperature	-40 to 70 °C (-40 to 158 °F)
Tcase max	80 °C measured at Tcase point
Tcase life	38 °C measured at Tcase point
Storage temperature	-40 to 85 °C (-40 to 185 °F)
Relative humidity	5 to 95% non-condensing

### Lifetime

90% survivals after 15 years continuous operation (125,000 hours) at Tcase-life.

### Certificates and Standards

Approval markings	CE, UKCA, ENEC
Operability markings	D4i
Ingress protection classification	IP66 (installed condition for CT node only in combination with NEMA compatible receptacle)
Impact resistance classification	IK08

### Sustainability

RoHS directive	2011/65/EU
Hazardous substances	Directive 2011/65/EU, as amended by Directive (EU) 2015/863 of March 2015
Chemical substances	REACH Directive 2006/1907/EC
Electronic waste	WEEE Directive 2012/19/EU

### Radio Equipment Directive 2014/53/EU

Safety (lighting equipment)	IEC/EN 61347-1 IEC/EN 61347-2-11
Safety (IT equipment)	IEC/EN 62368-1
EMC (lighting equipment)	EN 55015, EN 61547
EMC (IT equipment)	EN 55032, EN 55035
EMC (telecommunication)	ETSI EN 301 489-1 ETSI EN 301 489-52
EMC (GPS)	ETSI EN 301 489-1 ETSI EN 301 489-19
RF (telecommunication)	ETSI EN 301 511 ETSI EN 301 908-1 ETSI EN 301 908-13
RF (GPS)	EN 303 413
RF exposure	This device meets the EU requirements (2014/53/EU) on the limitation of exposure of the general public to electromagnetic fields by way of health protection. The device complies with RF specifications when the device used is at 321 mm from your body. EN 62311



## Ordering Data

Type	Order code
LLC7813/00 CT NODE NEMA5 ACLV P EU4VF LG	9137 010 66903

© 2023 Signify Holding. All rights reserved. Specifications are subject to change without notice. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.



[www.philips.com/lighting](http://www.philips.com/lighting)