



The continuous linear light solution

COB LED strip

COB LED strip delivers desirable linear light effect with extremely good uniformity and superior light quality. The product is a safe and reliable linear solution to fit various applications

Benefits

- Continuous linear light effect
- Comfortable light
- Long lifetime

Features

- Extremely good uniformity
- Superior light quality
- Safe and reliable

Application

- Home application
- Cabinet
- Corridors & stairways


COB LED strip

Versions



LS161 COB ON 4000K 5M

Dimensional drawing



Light Technical	
Color rendering index (CRI)	90
Operating and Electrical	
Input Voltage	24 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-10 to +40 °C

Light Technical

Order Code	Full Product Name	Correlated Color	
		Temperature (Nom)	Luminous Flux
929004121112	LS161 COB LED8 8.5W 930 5M	3000 K	720 lm
	24V		
929004121312	LS161 COB LED12 13W 930 5M	3000 K	1,050 lm
	24V		

Order Code	Full Product Name	Correlated Color	
		Temperature (Nom)	Luminous Flux
929004121212	LS161 COB LED8 8.5W 940 5M	4000 K	800 lm
	24V		
929004121412	LS161 COB LED12 13W 940 5M	4000 K	1,200 lm
	24V		

Operating and Electrical

Order Code	Full Product Name	Power Consumption
929004121112	LS161 COB LED8 8.5W 930 5M 24V	35 W
929004121312	LS161 COB LED12 13W 930 5M 24V	45 W
929004121212	LS161 COB LED8 8.5W 940 5M 24V	35 W
929004121412	LS161 COB LED12 13W 940 5M 24V	45 W

